


2




4 mm  
5/32 IN

18 ± 2 mm  
23/32 ± 1/16 IN



4 M = 6 Nm  
53 LB.-IN.



3

Cu 1x10...70 mm  
Cu 2x10...35 mm  
Cu 2x8 - 2 AWG  
Cu 1x8 - 2/0 AWG