



中国国家强制性产品认证证书

证书编号: 2008010302317033

委托人名称、地址

ABB Oy, Low Voltage Products
Muottitie 2A, P.O.Box 622, FIN-65101 VAASA (芬兰)

生产者(制造商)名称、地址

ABB Oy, Low Voltage Products
Muottitie 2A, P.O.Box 622, FIN-65101 VAASA (芬兰)

生产企业名称、地址

ABB Oy, Low Voltage Products
Muottitie 2A, P.O.Box 622, FIN-65101 VAASA (芬兰)

产品名称和系列、规格、型号

隔离开关

OT16F, OT16FT, OT16M, OT25F, OT25FT, OT25M, OT40F, OT40FT, OT40M, OT40ML; 详见参数附件

产品标准和技术要求

GB 14048.3-2008

上述产品符合强制性产品认证实施规则
CNCA-01C-011:2007的要求, 特发此证。

发证日期: 2010年12月15日 有效期至: 2015年12月15日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书, 证书首次颁发日期: 2008年12月29日

本证书的相关信息可通过国家认监委网站www.cnca.gov.cn查询



主任:

中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>



Q 0346126



中国国家强制性产品认证证书

附录:

证书编号: 2008010302317033

第 1 页 共 3 页

纸号: 346126

OT16F, OT16FT, OT16M, OT25F, OT25FT, OT25M, OT40F, OT40FT, OT40M,
OT40ML

OT16F, OT16FT

Ith:25A

Ue/Ie:415/500/690V/16A(AC-21A, AC-22A)

415/500V/16A, 690V/10A (AC-23A)

OT16M

Ith:25A

Ue/Ie:415V/16A

OT25F, OT25FT

Ith:32A

Ue/Ie:415/500/690V/25A (AC-21A, AC-22A)

415/500V/20A, 690V/11A (AC-23A)

OT25M

Ith:32A

Ue/Ie:415V/25A(AC-21A, AC-22A)

415V/20A (AC-23A)

OT40F, OT40FT

Ith:40A

Ue/Ie: 415/500/690V/40A (AC-21A, AC-22A)

415/500V/23A, 690V/12A (AC-23A)

OT40M

Ith:40A

Ue/Ie:415V/40A (AC-21A, AC-22A)

415V/23A (AC-23A)

注: 此附录与证书同时使用时有效。



主任:

中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>





中国国家强制性产品认证证书

附录:

证书编号: 2008010302317033

第 2 页 共 3 页

纸号: 346126

OT40ML

Ith: 40A

Ue/Ie: 400V/40A (AC-21A, AC-22A)

400V/23A (AC-23A)

Ui: 750V

Icw: 500A 1s

Icm(峰值): 705A

额定限制短路电流:

400V/50kA (OT40ML), 415V/50kA (OT16M, OT25M, OT40M),

690V/50kA (OT16F/FT, OT25F/FT, OT40F/FT)

AC-21A, AC-22A, AC-23A

3P, 4P

注: 此附录与证书同时使用时有效。



主任:

中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>





中国国家强制性产品认证证书

附录：
证书编号：2008010302317033

第 3 页 共 3 页
纸号：346126

OT	16	FT	3	N1	Mounting of the 4th pole N1=left side, N2=right side, blanco=symmetrical 4th pole
					Number of poles 3--3pole 4--4pole 6--parallel connection by 2 of 3 pole switch disconnectors 8--parallel connection by 2 of 4 pole switch disconnectors
					Structure F Base& DIN-rail mounting FT Door mounting M Base& DIN-rail mounting(415V rating, grey body) ML Base& DIN-rail mounting(400V rating, white body)
					Rated current 16A,25A,40A
					Switch disconnector

注：此附录与证书同时使用时有效。



主任：

中国质量认证中心

中国·北京·南四环西路188号9区 100070

<http://www.cqc.com.cn>





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

No. : 2008010302317033

NAME AND ADDRESS OF THE APPLICANT

ABB Oy, Low Voltage Products
Muottitie 2A, P.O.Box 622, FIN-65101 VAASA, Finland

NAME AND ADDRESS OF THE MANUFACTURER

ABB Oy, Low Voltage Products
Muottitie 2A, P.O.Box 622, FIN-65101 VAASA, Finland

NAME AND ADDRESS OF THE FACTORY

ABB Oy, Low Voltage Products
Muottitie 2A, P.O.Box 622, FIN-65101 VAASA, Finland

NAME, MODEL AND SPECIFICATION

Switch-disconnector

OT16F, OT16FT, OT16M, OT25F, OT25FT, OT25M, OT40F, OT40FT, OT40M, OT40ML; See the Appendix

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB 14048.3-2008

This is to certify that the above mentioned products have met the requirements of implementation rules for compulsory certification(REF NO. CNCA-01C-011:2007).

Date of issue: Dec. 15, 2010 Date of expiry: Dec. 15, 2015

Validity of this certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original certification: Dec. 29, 2008

This certificate can be verified through CNCA's website: www.cnca.gov.cn



President:

Wang Kejiao



CHINA QUALITY CERTIFICATION CENTRE

Section 9, No. 188, Nansihuan Xilu, Beijing 100070 P.R.China

<http://www.cqc.com.cn>