



L

IEC

Sezione Cavo
Wire Size
导线截面积

mm² 35 ÷ 95 Nm 13,5

7Nm

9Nm

1,1 Nm

7Nm

6Nm

T1/UEP 40

6Nm

Cu

Sezione Cavo
Wire Size
导线截面积

mm ²	Max	70	50
	Min	2,5	2,5
	Nm	7	7

IEC

AWG

Sezione Cavo
Wire Size
导线截面积

lb in	14-10	20
	8	40
	6-1/0	45

UL

AlCu

7Nm

9Nm

T1/UEP 80

9Nm

8Nm

