

Manual motor starters MS132/MS116

Manual motor starter

Type old	Order code old	Range old	Type new	Order code new	Range new
MS225-0.16	1SAM 151 000 R1001	0.10 - 0.16 A	MS116-0.16	1SAM 250 000 R1001	0.10 - 0.16 A
MS225-0.25	1SAM 151 000 R1002	0.16 - 0.25 A	MS116-0.25	1SAM 250 000 R1002	0.16 - 0.25 A
MS225-0.4	1SAM 151 000 R1003	0.25 - 0.40 A	MS116-0.4	1SAM 250 000 R1003	0.25 - 0.40 A
MS225-0.63	1SAM 151 000 R1004	0.40 - 0.63 A	MS116-0.63	1SAM 250 000 R1004	0.40 - 0.63 A
MS225-1	1SAM 151 000 R1005	0.63 - 1.00 A	MS116-1.0	1SAM 250 000 R1005	0.63 - 1.00 A
MS225-1.6	1SAM 151 000 R1006	1.00 - 1.60 A	MS116-1.6	1SAM 250 000 R1006	1.00 - 1.60 A
MS225-2.5	1SAM 151 000 R1007	1.60 - 2.50 A	MS116-2.5	1SAM 250 000 R1007	1.60 - 2.50 A
MS225-4	1SAM 151 000 R1008	2.50 - 4.00 A	MS116-4.0	1SAM 250 000 R1008	2.50 - 4.00 A
MS225-6.3	1SAM 151 000 R1009	4.00 - 6.30 A	MS116-6.3	1SAM 250 000 R1009	4.00 - 6.30 A
MS225-9	1SAM 151 000 R1010	6.30 - 9.00 A	MS116-10	1SAM 250 000 R1010	6.30 - 10.0 A
MS225-12.5	1SAM 151 000 R1011	9.00 - 12.5 A	MS116-12	1SAM 250 000 R1012	8.00 - 12.0 A
MS225-16	1SAM 151 000 R1012	12.5 - 16.0 A	MS116-16	1SAM 250 000 R1011	10.0 - 16.0 A
MS225-20	1SAM 151 000 R1013	16.0 - 20.0 A	MS116-20	1SAM 250 000 R1013	16.0 - 20.0 A
MS225-25	1SAM 151 000 R1014	20.0 - 25.0 A	MS116-25	1SAM 250 000 R1014	20.0 - 25.0 A
			MS116-32	1SAM 250 000 R1015	25.0 - 32.0 A

Type old	Order code old	Range old	Type new	Order code new	Range new
MS325-0.16	1SAM 150 000 R1001	0.10 - 0.16 A	MS132-0.16	1SAM 350 000 R1001	0.10 - 0.16 A
MS325-0.25	1SAM 150 000 R1002	0.16 - 0.25 A	MS132-0.25	1SAM 350 000 R1002	0.16 - 0.25 A
MS325-0.4	1SAM 150 000 R1003	0.25 - 0.40 A	MS132-0.4	1SAM 350 000 R1003	0.25 - 0.40 A
MS325-0.63	1SAM 150 000 R1004	0.40 - 0.63 A	MS132-0.63	1SAM 350 000 R1004	0.40 - 0.63 A
MS325-1	1SAM 150 000 R1005	0.63 - 1.00 A	MS132-1.0	1SAM 350 000 R1005	0.63 - 1.00 A
MS325-1.6	1SAM 150 000 R1006	1.00 - 1.60 A	MS132-1.6	1SAM 350 000 R1006	1.00 - 1.60 A
MS325-2.5	1SAM 150 000 R1007	1.60 - 2.50 A	MS132-2.5	1SAM 350 000 R1007	1.60 - 2.50 A
MS325-4	1SAM 150 000 R1008	2.50 - 4.00 A	MS132-4.0	1SAM 350 000 R1008	2.50 - 4.00 A
MS325-6.3	1SAM 150 000 R1009	4.00 - 6.30 A	MS132-6.3	1SAM 350 000 R1009	4.00 - 6.30 A
MS325-9	1SAM 150 000 R1010	6.30 - 9.00 A	MS132-10	1SAM 350 000 R1010	6.30 - 10.0 A
MS325-12.5	1SAM 150 000 R1011	9.00 - 12.5 A	MS132-12	1SAM 350 000 R1012	8.00 - 12.0 A
MS325-16	1SAM 150 000 R1012	12.5 - 16.0 A	MS132-16	1SAM 350 000 R1011	10.0 - 16.0 A
MS325-20	1SAM 150 000 R1013	16.0 - 20.0 A	MS132-20	1SAM 350 000 R1013	16.0 - 20.0 A
MS325-25	1SAM 150 000 R1014	20.0 - 25.0 A	MS132-25	1SAM 350 000 R1014	20.0 - 25.0 A
			MS132-32	1SAM 350 000 R1015	25.0 - 32.0 A

Type old	Order code old	Range old	Type new	Order code new	Range new
MS450-16	1SAM 450 000 R1001	11.0 - 16.0 A	MS132-16	1SAM 350 000 R1011	10.0 - 16.0 A
MS450-20	1SAM 450 000 R1002	14.0 - 20.0 A	MS132-20	1SAM 350 000 R1013	16.0 - 20.0 A
MS450-25	1SAM 450 000 R1003	18.0 - 25.0 A	MS132-25	1SAM 350 000 R1014	20.0 - 25.0 A
MS450-32	1SAM 450 000 R1004	22.0 - 32.0 A	MS132-32	1SAM 350 000 R1015	25.0 - 32.0 A

Manual motor starter

Type old	Order code old	Type new	Order code new
		MO132-0.16	1SAM 360 000 R1001
		MO132-0.25	1SAM 360 000 R1002
MO325-0.4	1SAM 160 000 R1003	MO132-0.4	1SAM 360 000 R1003
MO325-0.63	1SAM 160 000 R1004	MO132-0.63	1SAM 360 000 R1004
MO325-1	1SAM 160 000 R1005	MO132-1.0	1SAM 360 000 R1005
MO325-1.6	1SAM 160 000 R1006	MO132-1.6	1SAM 360 000 R1006
MO325-2.5	1SAM 160 000 R1007	MO132-2.5	1SAM 360 000 R1007
MO325-4	1SAM 160 000 R1008	MO132-4.0	1SAM 360 000 R1008
MO325-6.3	1SAM 160 000 R1009	MO132-6.3	1SAM 360 000 R1009
MO325-9	1SAM 160 000 R1010	MO132-10	1SAM 360 000 R1010
MO325-12.5	1SAM 160 000 R1011	MO132-12	1SAM 360 000 R1012
MO325-16	1SAM 160 000 R1012	MO132-16	1SAM 360 000 R1011
MO325-20	1SAM 160 000 R1013	MO132-20	1SAM 360 000 R1013
MO325-25	1SAM 160 000 R1014	MO132-25	1SAM 360 000 R1014
		MO132-32	1SAM 360 000 R1015

Type old	Order code old	Type new	Order code new
MO450-16	1SAM 460 000 R1001	MO132-16	1SAM 360 000 R1011
MO450-20	1SAM 460 000 R1002	MO132-20	1SAM 360 000 R1013
MO450-25	1SAM 460 000 R1003	MO132-25	1SAM 360 000 R1014
MO450-32	1SAM 460 000 R1004	MO132-32	1SAM 360 000 R1015

Busbars

Type old	Order code old	Type new	Order code new
PS1-2-0	1SAM 201 906 R1002	PS1-2-0-65	1SAM 201 906 R1102
PS1-3-0	1SAM 201 906 R1003	PS1-3-0-65	1SAM 201 906 R1103
PS1-4-0	1SAM 201 906 R1004	PS1-4-0-65	1SAM 201 906 R1104
PS1-5-0	1SAM 201 906 R1005	PS1-5-0-65	1SAM 201 906 R1105
PS1-2-1	1SAM 201 906 R1012	PS1-2-1-65	1SAM 201 906 R1112
PS1-3-1	1SAM 201 906 R1013	PS1-3-1-65	1SAM 201 906 R1113
PS1-4-1	1SAM 201 906 R1014	PS1-4-1-65	1SAM 201 906 R1114
PS1-5-1	1SAM 201 906 R1015	PS1-5-1-65	1SAM 201 906 R1115
PS1-2-2	1SAM 201 906 R1022	PS1-2-2-65	1SAM 201 906 R1122
PS1-3-2	1SAM 201 906 R1023	PS1-3-2-65	1SAM 201 906 R1123
PS1-4-2	1SAM 201 906 R1024	PS1-4-2-65	1SAM 201 906 R1124
PS1-5-2	1SAM 201 906 R1025	PS1-5-2-65	1SAM 201 906 R1125
S1-M1	1SAM 201 907 R1001	S1-M1-25	1SAM 201 907 R1101
S1-M2	1SAM 201 907 R1002	S1-M2-25	1SAM 201 907 R1102

Accessories

Type old	Order code old	Type new	Order code new
DMS116-Y	1SAM 201 912 R1001	DMS132-Y	1SAM 201 912 R1011
DMS116-G	1SAM 201 912 R1000	DMS132-G	1SAM 201 912 R1010
IB116-F	1SAM 201 911 R1002	IB132-F	1SAM 201 911 R1012
IB116-Y	1SAM 201 911 R1001	IB132-Y	1SAM 201 911 R1011
IB116-G	1SAM 201 911 R1000	IB132-G	1SAM 201 911 R1010
MSOX-32, 5mm	1SAM 101 924 R0002	MSOX-32, 6mm	1SAM 101 924 R0003
MSOX-30, 5mm	1SAM 101 924 R0012	MSOX-30, 6mm	1SAM 101 924 R0013
MSMN	1SAM 101 923 R0001	MSMN	1SAM 101 923 R0002
		MSMNO	1SAM 101 923 R0012

Contact us

ABB STOTZ-KONTAKT GmbH

Eppelheimer Straße 82
D-69123 Heidelberg
P. O. Box 10 16 80
D-69006 Heidelberg

You can find the address of your
local sales organisation on the
ABB home page
<http://www.abb.com/contacts>
-> Low Voltage products

Note:

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB AG does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB AG.

Copyright© 2011 ABB
All rights reserved