



ROHS DECLARATION OF CONFORMITY

We ABB France - Chassieu
Division Produits Automation
Activité Raccordement
10 rue Ampères
ZI
BP114
69685 CHASSIEU Cedex
France

Declare that the product listed below.

Type: Screw Clamp Terminal block

To which this declaration relates, is following the provisions of EU Directive(s)

2002/95/EC applicable on Restriction of Hazardous Substances (RoHS), amended by the Commission Decision of 18 August 2005, 2005/618/EC.

The products are not in the product list of the RoHS directive. But in some case they are components of concerned equipments.

Nevertheless that the product are made RoHS compliant, The responsibility for the concerned equipment remains with the manufacturer of it

The declaration is subject to the provision of the respective delivery contact.

Chassieu,

Yannick VILLARDIER
Quality Development

Bernard BECHAZ
Technical Manager



ROHS DECLARATION OF CONFORMITY

Part Number	Description
1SNA105002R2000	M4/6
1SNA105003R2100	M4/6 C1 JAUNE
1SNA105004R2200	M6/8
1SNA105044R2100	M4/6.D2
1SNA105045R2200	M4/6.D2
1SNA105046R2300	M4/6.D2
1SNA105047R2400	M4/6.D2
1SNA105048R0500	M4/6.D2
1SNA105049R0600	M4/6.D2
1SNA105051R2000	M4/6
1SNA105052R2100	MA2.5/5
1SNA105054R2300	M4/6.SNBT4
1SNA105058R0700	M 6/8 SNB ORANGE
1SNA105060R0500	MB 6/8 L2 JAUNE
1SNA105075R2000	MA2.5/5
1SNA105077R2200	MA2.5/5
1SNA105118R2000	M6/8
1SNA105120R2600	M10/10
1SNA105128R2200	M6/8.1
1SNA105139R2500	DA 2.5/5.NOIR V2
1SNA105140R0200	D4/6.NOIR V2
1SNA105208R1300	M 4/6.1 ORANGE
1SNA107250R1200	M 4/6 SNB
1SNA110106R2500	DR1.5/4
1SNA110251R0500	DR4/6
1SNA110331R2500	D4/6.LNTP6
1SNA110366R0000	D 4/6 LNTP9 (3L 1P)
1SNA110368R1200	DR4/8SF
1SNA110440R0700	D4/6.NLP
1SNA110441R2400	D4/6.LLP
1SNA110442R2500	D4/6.LL
1SNA110447R2200	D4/6.NL
1SNA110449R0400	D4/6.L
1SNA110491R1700	DR4/6.1
1SNA111296R1000	E10/16 S
1SNA112086R0200	DR1.5/5.1
1SNA112097R0500	DR2.5/5.S
1SNA115116R0700	M4/6
1SNA115118R1100	M6/8
1SNA115120R1700	M10/10
1SNA115124R0700	M35/16
1SNA115126R0100	M4/6.D2.1
1SNA115129R1400	M16/12
1SNA115192R0400	M4/6.4
1SNA115204R2000	M4/6.D1.1
1SNA115216R1300	M70/22



ROHS DECLARATION OF CONFORMITY

1SNA115224R1300	M4/6.T
1SNA115228R2700	M10/10.C
Part Number	Description
1SNA115237R1000	M6/8.ST1
1SNA115239R2200	M6/8.ST3
1SNA115243R2600	M6/8.ST7
1SNA115253R2000	M6/8.3
1SNA115260R0300	M6/8.1
1SNA115261R2000	M10/10.1
1SNA115265R2400	MS4/6
1SNA115268R0700	M4/6.3
1SNA115269R0000	M4/6.D2.3
1SNA115271R2200	M4/6.D2
1SNA115272R2300	MB 4/6 D2. 1
1SNA115322R1500	M4/6.D2.2
1SNA115328R2300	MB10/10.L2
1SNA115329R2400	MB10/10.L3
1SNA115330R2100	MB10/10.L4
1SNA115331R1600	MB10/10.L5
1SNA115332R1700	MB10/10.L6
1SNA115333R1000	MB10/10.L8
1SNA115334R1100	MB10/10.L10
1SNA115359R0200	M6/8.STA
1SNA115367R2200	M 4/6.10 R
1SNA115368R0300	M 6/8.10 R
1SNA115377R2400	M10/16.SF
1SNA115379R0600	M10/16.SN
1SNA115406R1300	MB4/6.L2
1SNA115407R1400	MB4/6.L3
1SNA115408R2500	MB4/6.L4
1SNA115409R2600	MB4/6.L5
1SNA115410R1200	MB4/6.L6
1SNA115411R0700	MB4/6.L8
1SNA115412R0000	MB4/6.L10
1SNA115413R0100	MB6/8.L2
1SNA115414R0200	MB6/8.L3
1SNA115415R0300	MB6/8.L4
1SNA115416R0400	MB6/8.L5
1SNA115417R0500	MB6/8.L6
1SNA115418R1600	MB6/8.L8
1SNA115419R1700	MB6/8.L10
1SNA115435R0700	M4/6.SB
1SNA115436R0000	M6/8.SB
1SNA115438R1200	M 4/6 SNBT1
1SNA115441R1500	M 4/6 SNBT2
1SNA115468R2000	M4/6.3A
1SNA115474R1600	M10/10.4
1SNA115479R2300	M4/6.4A
1SNA115485R0200	MA2.5/5.1



ROHS DECLARATION OF CONFORMITY

1SNA115486R0300	MA2.5/5
1SNA115490R1300	MA2.5/5.D2
Part Number	Description
1SNA115491R0000	MA2.5/5.D2.1
1SNA115492R0100	MA2.5/5.2
1SNA115495R0400	M4/6.SNBT23
1SNA115499R1000	M6/8.STP2
1SNA115501R1200	M6/8.D2
1SNA115506R1700	MA2.5/5.SB
1SNA115509R2200	MA 2.5/5 SNBT
1SNA115529R1500	M6/8.STP1
1SNA115530R1200	MA2.5/5.D1.1
1SNA115532R0000	D2.5/6 DPA
1SNA115537R0500	D2.5/6.DL
1SNA115538R1600	D2.5/6.DL1
1SNA115541R1100	D2.5/6.DA
1SNA115542R1200	D2.5/6.D
1SNA115556R1000	M95/26
1SNA115580R1500	MB6/8 L2.4
1SNA115604R2100	M4/8.D2.SF
1SNA115617R1500	M4/6.D2.4
1SNA115642R2600	D2.5/6.DPAL1
1SNA115643R2700	D2.5/6.DPA1
1SNA115646R2200	M4/8.D2.SFL
1SNA115649R0500	M4/8.D2.SFLJ
1SNA115657R2500	M4/8.SF
1SNA115659R0700	M4/8.SN
1SNA115660R0400	M4/8.SN1
1SNA115661R2100	M4/8.SFL
1SNA115662R2200	M4/8.SFT
1SNA115667R2700	M4/8.SFLT
1SNA115668R0000	M4/8.SNT
1SNA115687R1400	M4/6.SNBT4
1SNA115688R2500	M6/8.SNB
1SNA115691R1000	M 6/8S SNB GRIS
1SNA115692R1100	M4/8.D2.SFJ
1SNA115699R2000	MA2.5/5.SNB
1SNA115700R0500	MA2.5/5.SNBT
1SNA115970R2300	M 6/8 ST8
1SNA115971R1000	M6/8.ST1.V2.IP20
1SNA115986R0000	M4/6.SNB
1SNA115987R0100	M4/6.SNBT
1SNA116298R2700	MB10/24.SF1
1SNA120251R0700	DR4/6.N
1SNA125116R0100	M4/6.N
1SNA125118R1300	M6/8.N
1SNA125120R1100	M10/10.N
1SNA125124R0100	M35/16.N
1SNA125126R0300	M4/6.D2.1.N



ROHS DECLARATION OF CONFORMITY

1SNA125129R1600	M16/12.N
1SNA125216R1500	M70/22.N
Part Number	Description
1SNA125265R2600	MS4/6.N
1SNA125278R0300	MS6/8.N
1SNA125297R1700	MB 4/6 L3-1 BLEU
1SNA125328R2500	MB 10/10 N2
1SNA125468R2200	M4/6.3A.N
1SNA125479R2500	M4/6.4A.N
1SNA125485R0400	MA2.5/5.1.N
1SNA125486R0500	MA2.5/5.N
1SNA125487R0600	M2.5/5.NT
1SNA125490R1500	MA2.5/5.D2.N
1SNA125491R0200	MA2.5/5.D2.1.N
1SNA125530R1400	MA2.5/5.D1.1.N
1SNA125541R1300	D2.5/6.DA.N
1SNA125556R1200	M95/26.N
1SNA125593R0000	M16/12.NT1
1SNA125686R1500	M4/6.SNB
1SNA140000R1000	M4/6.NC
1SNA140001R0500	M4/6.N.NC
1SNA140002R0600	M4/6.NC
1SNA140003R0700	M4/6.NC
1SNA140004R0000	M4/6.NC
1SNA140013R2000	M4/8.SFLT.NC
1SNA140016R2300	M6/8.NC
1SNA140017R2400	M6/8.N.NC
1SNA140019R0600	M4/6.D2.NC
1SNA140020R0300	M4/6.D2.1.NC
1SNA140021R2000	M6/8.D2.NC
1SNA140023R2200	M4/6.NC
1SNA140026R2500	M4/6.NC
1SNA140027R2600	M6/8.NC
1SNA140028R0700	M6/8.NC
1SNA140033R2400	M4/8.SF.NC
1SNA140038R0100	M4/6.3A.NC
1SNA146001R2700	M 4/6.Ex
1SNA146002R2000	M 4/6 N.Ex
1SNA146003R2100	M 6/8.Ex
1SNA146004R2200	M 6/8 N.Ex
1SNA146005R2300	M10/10.Ex
1SNA146006R2400	M 10/10 N.Ex
1SNA146009R0700	M4/6.D2.Ex
1SNA146010R2300	M 4/6 3A.Ex
1SNA146011R1000	M 4/6 3A.N.Ex
1SNA146012R1100	M4/6 4A.Ex
1SNA146013R1200	M 4/6 A4.N.Ex
1SNA146014R1300	MA2.5/5.Ex
1SNA146015R1400	MA2.5/5.N.Ex



ROHS DECLARATION OF CONFORMITY

1SNA146017R1600	MA2.5/5.D2.Ex
1SNA146018R2700	MA2.5/5.D2.N.Ex
Part Number	Description
1SNA146019R2000	MA2.5/5.D2.1.Ex
1SNA146020R2500	M 95/26.Ex
1SNA146021R1200	BLOC M10/10P.Ex
1SNA146023R1400	M4/6.P.Ex
1SNA146024R1500	M95/26 N.Ex
1SNA146025R1600	M 70/22.Ex
1SNA146026R1700	M70/22.N.Ex
1SNA146027R1000	M16/12.Ex
1SNA146028R2100	M 16/12 N.Ex
1SNA146043R2000	M16/12.P.Ex
1SNA146044R2100	M35/16.P.Ex
1SNA146068R0100	M95/26.P.Ex
1SNA146073R2600	M70/22.P.Ex
1SNA146098R2000	D2.5/6-DA.EX
1SNA146104R2300	D2.5/6-DA.N.EX
1SNA146200R1700	DR 4/6.1.Ex
1SNA146237R2700	M 4/6 PI.Ex
1SNA146238R0000	M 6/8 PI.Ex
1SNA146239R0100	M 10/10 PI.Ex
1SNA146240R1600	MA2.5/5.PI.Ex
1SNA146245R0700	M 4/6.Ex
1SNA146283R2600	M4/6.D2.1.N.EX
1SNA146285R2000	M 4/6.Ex
1SNA146291R2600	M16/12.PI.Ex
1SNA160496R2600	DR4/6.P
1SNA162855R2300	E10/13.P
1SNA162911R1300	COSSE DE MASSE DIN2
1SNA165111R1400	M35/16.P
1SNA165113R1600	M4/6.P
1SNA165114R1700	M6/8.P
1SNA165115R1000	M10/10.P
1SNA165130R2300	M16/12.P
1SNA165275R0000	M4/6.PI
1SNA165343R0400	MB10/10.P2
1SNA165344R0500	MB10/10.P3
1SNA165345R0600	MB10/10.P4
1SNA165346R0700	MB10/10.P5
1SNA165347R0000	MB10/10.P6
1SNA165348R1100	MB10/10.P8
1SNA165349R1200	MB10/10.P10
1SNA165420R2600	MB4/6.P2
1SNA165421R1300	MB4/6.P3
1SNA165423R1500	MB4/6.P5
1SNA165424R1600	MB4/6.P6
1SNA165425R1700	MB4/6.P8
1SNA165426R1000	MB4/6.P10



ROHS DECLARATION OF CONFORMITY

1SNA165427R1100	MB6/8.P2
1SNA165428R2200	MB6/8.P3
Part Number	Description
1SNA165429R2300	MB6/8.P4
1SNA165430R2000	MB6/8.P5
1SNA165431R1500	MB6/8.P6
1SNA165432R1600	MB6/8.P8
1SNA165433R1700	MB6/8.P10
1SNA165453R2300	M16/12.PI
1SNA165488R2700	MA2.5/5.P
1SNA165596R1300	M70/22.PI
1SNA165677R0300	MA2.5/5.PI
1SNA165683R2200	M10/10.PE.N
1SNA165809R0100	D4/6.P
1SNA165830R2100	D6/8.P
1SNA165909R0500	D2.5/5.P
1SNA180558R0000	BLOC 81H IC VV
1SNA180559R0100	BLOC 81H IB VV
1SNA190607R0400	E6/8 V0 - 7.963.1114
1SNA191302R2700	E10/16 V0 - 7.963.1110
1SNA195111R0300	M35/16.P.V0
1SNA195115R0700	M10/10.P.V0
1SNA195116R0000	M4/6.V0
1SNA195118R1200	M6/8.V0
1SNA195120R1000	M10/10.V0
1SNA195124R0000	M35/16.V0
1SNA195126R0200	M4/6.D2.1.V0
1SNA195129R1500	M16/12.V0
1SNA195130R1200	M16/12.P.V0
1SNA195209R0600	M6/8.C.V0
1SNA195210R2200	M16/12.C.V0
1SNA195219R2700	M6/8.4.V0
1SNA195224R1400	M4/6.T.V0
1SNA195228R2000	M10/10.V0
1SNA195236R1000	M6/8.ST.V0
1SNA195237R1100	M6/8.ST1.V0
1SNA195240R0000	M6/8.ST4.V0
1SNA195241R2500	M6/8.ST5.V0
1SNA195242R2600	M6/8.ST6.V0
1SNA195243R2700	M6/8.ST7.V0
1SNA195253R2100	M6/8.3.V0
1SNA195259R0700	M4/6.1.V0
1SNA195260R0400	M6/8.1.V0
1SNA195261R2100	M10/10.1.V0
1SNA195265R2500	MS4/6.V0
1SNA195268R0000	M4/6.3.V0
1SNA195271R2300	M4/6.D2.V0
1SNA195313R1500	M4/6.ST.Sn.V0
1SNA195315R1700	M4/8.5.STI.Sn.V0



ROHS DECLARATION OF CONFORMITY

1SNA195322R1600	M4/6.D2.2.V0
1SNA195359R0300	M6/8.STA.V0
Part Number	Description
1SNA195435R0000	M4/6.SB.V0
1SNA195436R0100	M6/8.SB.V0
1SNA195468R2100	M4/6.3A.V0
1SNA195479R2400	M4/6.4A.V0
1SNA195480R1200	M4/6.SNBT.4A.V0
1SNA195486R0400	MA2.5/5.V0
1SNA195490R1400	MA2.5/5.D2.V0
1SNA195501R1300	M6/8.D2.V0
1SNA195556R1100	M95/26.V0
1SNA195604R2200	M4/8.D2.SF.V0
1SNA195637R1200	M4/6.3A.P.V0
1SNA195640R0100	M6/8.ST.V0.IP20
1SNA195657R2600	M4/8.SF.V0
1SNA195660R0500	M4/8.SN1.V0
1SNA195662R2300	M4/8.SFT.V0
1SNA195668R0100	M4/8.SNT.V0
1SNA195924R0200	M10/10.ST1.V0
1SNA195925R0300	M10/10 ST VO
1SNA199004R2000	M10/10.N.V0
1SNA199005R2100	M16/12.N.V0
1SNA199011R1600	MU10/14.5.SF1
1SNA199012R1700	MU10/13.SF1
1SNA199013R1000	MU10/14.5.SF2
1SNA199015R1200	MU10/14.5.SN3
1SNA199021R1000	MU10/13.SN3
1SNA199095R1300	ML10/13.SF
1SNA199105R2200	ML10/13.SN
1SNA199168R0000	ML10/13.SFL
1SNA199219R0300	D4/6.T1
1SNA199220R0000	D4/6.P.T1
1SNA199444R2500	M4/6.D2.2S2
1SNA199447R2000	M4/6.D2.2S2.T23
1SNA199448R0100	M4/6.D2.2S2.T
1SNA199452R2500	M4/6.D2.S1R
1SNA199455R2000	M4/6.D2.S1R.T23
1SNA199456R2100	M4/6.D2.S1R.T
1SNA206303R1700	MB 6/8 L2 GRIS SANS FLASQUE
1SNA206304R1000	MB 6/8 L3 N SANS FLASQUE BLEU
1SNA206404R0500	M4/6
1SNA206538R0200	M4/6.SNBT
1SNA215116R1300	D4/6
1SNA215118R2500	D6/8
1SNA215129R2000	D 16/12
1SNA215486R1700	DA2.5/5
1SNA299683R0100	D4/6.T3
1SNA299684R0200	D4/6.T3.P



ROHS DECLARATION OF CONFORMITY

1SNA299838R0400	D4/6.P.V0
1SNA399024R2300	M70/22.P
Part Number	Description
1SNA399176R0000	M95/26.P
1SNA399575R0000	DR1.5/4.V0
1SNA399578R1300	DR1.5/4.1.V0
1SNA399704R1200	D240/36.D10
1SNA399705R1300	D240/36.D10.PI
1SNA399706R1400	D240/36.D10.N
1SNA399715R0400	D150/31.D10
1SNA399716R0500	D150/31.D10.PI
1SNA399717R0600	D150/31.D10.N
1SNA399723R0400	M10/10.ST1.IP20
1SNA399724R0500	M10/10.ST.IP20
1SNA399815R2100	M4/8 SF2
1SNA399893R2000	M 4/6 VO MARRON
1SNA400014R2700	ES8-CG VERT 7.963.1383
1SNA400015R2000	ES8-CG IVOIRE 7.963.1377
1SNA400186R2100	M6/8
1SNA400187R2200	M6/8
1SNA400188R0300	M10/10
1SNA400189R0400	M10/10
1SNA400190R0100	M10/10
1SNA400191R2600	M16/12
1SNA400192R2700	M16/12
1SNA400193R2000	M16/12
1SNA400239R1500	M6/8
1SNA400256R1600	M 70/22 O
1SNA400257R1700	M 70/22 N. O
1SNA356100R1500	DBTI 7 DEPARTS SOCLE BLEU
1SNA356101R0200	DBTI 7 DEPARTS SOCLE VERT
1SNA356102R0300	DBTI 12 DEPARTS SOCLE BLEU
1SNA356103R0400	DBTI 12 DEPARTS SOCLE VERT

Manufactured after : April 1st, 2007

Yannick VILLARDIER
Quality Development

Bernard BECHAZ
Technical Manager