













# Tmax

DOC. N.° 1SDH000436R0631 - L3963


FLD - Frontale per blocchi T4-T5  
FLD - Front for T4-T5 locks  
FLD - Frontplatte für Verriegelungen T4-T5  
FLD - Frontal pour verrouillages T4-T5  
FLD - Frontal para bloques T4-T5  
FLD - 前面板T4-T5



**D****E****F****G**

**H****T5****I****T4****L****M**



N



max n° 3 Ø 6÷7 mm  
最多可挂三把 Ø 6-7 的锁




O

ONLY FOR T4 W



P

Blocco della porta della cella  
Compartment door interlock  
Verriegelung der Schaltfeldtür  
Verrouillage de la porte du compartiment  
Bloqueo (enclavamiento) de la puerta de la celda  
室门联锁



	A	B	C	D
WITH FLANGE CON MOSTRINA 带法兰	140.5	115	115.5	64.5
WITHOUT FLANGE SENZA MOSTRINA 不带法兰	140.5	107	107.5	60.5