



QQGQ2.E224058

Power Supplies, Information Technology Equipment Including Electrical Business Equipment - Component

[Page Bottom](#)[Questions?](#)

Power Supplies, Information Technology Equipment Including Electrical Business Equipment - Component

[Guide Information](#)

ABB STOTZ-KONTAKT GMBH
EPPELHEIMER STR 82
69123 HEIDELBERG 1, GERMANY

E224058

Model No.	Rated Input			Max Output							
	Volts	Hz	SC	V	A	VA	OC	SP	EP	FC	GC
CP - 24/10 adj[*r]											
	100-120/ 208-240ac	50/60	0	48	10	240	3	1950	15B	0	0
CP - 24/20 adj											
	100-120/ 208-240/ 115/ 230ac	50/60	0	56	21.5	566	3	1950	15B	0	1

[*r] - Output values are rated.

Marking: Company name and model designation.

[Page Top](#)[Notice of Disclaimer](#)[Questions?](#)

[UL Listed and Classified
Products](#)

[UL Recognized
Components](#)

[Products Certified
for Canada](#)

This page and all contents are Copyright © 2003 by Underwriters Laboratories Inc.®

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Listed and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained on UL's Website subject to the following conditions: 1. The Guide Information, Designs and/or Listings (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from Underwriters Laboratories Inc." must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "Copyright © 2003 Underwriters Laboratories Inc.®"