

Conversion table

Type old	Order code old	Type new	Ordercode new
----------	----------------	----------	---------------

Current monitoring relays, single-phase

CM-SRS	1SVR 430 841 R0100	CM-SRS.11	1SVR 430 841 R0200
CM-SRS	1SVR 430 841 R1100	CM-SRS.11	1SVR 430 841 R1200
CM-SRS	1SVR 430 841 R9100	CM-SRS.11	1SVR 430 840 R0200
CM-SRN	1SVR 450 110 R0000	CM-SRS.21	1SVR 430 841 R0400
CM-SRN	1SVR 450 110 R0100	CM-SRS.22	1SVR 430 841 R0500
CM-SRN	1SVR 450 111 R0000	CM-SRS.21	1SVR 430 841 R1400
CM-SRN	1SVR 450 111 R0100	CM-SRS.22	1SVR 430 841 R1500
CM-SRN	1SVR 450 115 R0000	CM-SRS.21	1SVR 430 840 R0400
CM-SRN	1SVR 450 115 R0100	CM-SRS.22	1SVR 430 840 R0500
CM-SRN	1SVR 450 120 R0000	CM-SRS.21	1SVR 430 841 R0400
CM-SRN	1SVR 450 120 R0100	CM-SRS.22	1SVR 430 841 R0500
CM-SRN	1SVR 450 121 R0000	CM-SRS.21	1SVR 430 841 R1400
CM-SRN	1SVR 450 121 R0100	CM-SRS.22	1SVR 430 841 R1500
CM-SRN	1SVR 450 125 R0000	CM-SRS.21	1SVR 430 840 R0400
CM-SRN	1SVR 450 125 R0100	CM-SRS.22	1SVR 430 840 R0500
C551.01	1SAR 411 010 R0001	CM-SRS.11	1SVR 430 840 R0200
C551.01	1SAR 411 010 R0002	CM-SRS.11	1SVR 430 840 R0200
C551.01	1SAR 411 010 R0003	CM-SRS.11	1SVR 430 840 R0200
C551.01	1SAR 411 010 R0004	CM-SRS.11	1SVR 430 841 R0200
C551.01	1SAR 411 010 R0005	CM-SRS.11	1SVR 430 841 R1200
C551.02	1SAR 412 010 R0001	CM-SRS.12	1SVR 430 840 R0300
C551.02	1SAR 412 010 R0002	CM-SRS.12	1SVR 430 840 R0300
C551.02	1SAR 412 010 R0003	CM-SRS.12	1SVR 430 840 R0300
C551.02	1SAR 412 010 R0004	CM-SRS.12	1SVR 430 841 R0300
C551.02	1SAR 412 010 R0005	CM-SRS.12	1SVR 430 841 R1300

Voltage monitoring relays, single-phase

CM-ESS	1SVR 430 831 R9000	CM-ESS.1	1SVR 430 830 R0300
CM-ESS	1SVR 430 831 R0000	CM-ESS.1	1SVR 430 831 R0300
CM-ESS	1SVR 430 831 R1000	CM-ESS.1	1SVR 430 831 R1300
CM-ESS	1SVR 430 831 R9100	CM-ESS.1	1SVR 430 830 R0300
CM-ESS	1SVR 430 831 R0100	CM-ESS.1	1SVR 430 831 R0300
CM-ESS	1SVR 430 831 R1100	CM-ESS.1	1SVR 430 831 R1300
CM-ESS	1SVR 430 831 R9200	CM-ESS.1	1SVR 430 830 R0300
CM-ESS	1SVR 430 831 R0200	CM-ESS.1	1SVR 430 831 R0300
CM-ESS	1SVR 430 831 R1200	CM-ESS.1	1SVR 430 831 R1300
CM-ESN	1SVR 450 210 R0000	CM-ESS.2	1SVR 430 831 R0400
CM-ESN	1SVR 450 211 R0000	CM-ESS.2	1SVR 430 831 R1400
CM-ESN	1SVR 450 215 R0000	CM-ESS.2	1SVR 430 830 R0400
CM-ESN	1SVR 450 220 R0000	CM-ESS.2	1SVR 430 831 R0400
CM-ESN	1SVR 450 221 R0000	CM-ESS.2	1SVR 430 831 R1400
CM-ESN	1SVR 450 225 R0000	CM-ESS.2	1SVR 430 830 R0400
CM-ESN	1SVR 450 210 R0100	CM-ESS.2	1SVR 430 831 R0400
CM-ESN	1SVR 450 211 R0100	CM-ESS.2	1SVR 430 831 R1400
CM-ESN	1SVR 450 215 R0100	CM-ESS.2	1SVR 430 830 R0400
CM-ESN	1SVR 450 220 R0100	CM-ESS.2	1SVR 430 831 R0400
CM-ESN	1SVR 450 221 R0100	CM-ESS.2	1SVR 430 831 R1400
CM-ESN	1SVR 450 225 R0100	CM-ESS.2	1SVR 430 830 R0400
CM-ESN	1SVR 450 210 R0200	CM-ESS.2	1SVR 430 831 R0400
CM-ESN	1SVR 450 211 R0200	CM-ESS.2	1SVR 430 831 R1400
CM-ESN	1SVR 450 215 R0200	CM-ESS.2	1SVR 430 830 R0400
CM-ESN	1SVR 450 220 R0200	CM-ESS.2	1SVR 430 831 R0400
CM-ESN	1SVR 450 221 R0200	CM-ESS.2	1SVR 430 831 R1400
CM-ESN	1SVR 450 225 R0200	CM-ESS.2	1SVR 430 830 R0400
CM-EFN	1SVR 450 200 R1100	CM-EFS	1SVR 430 750 R0400
CM-EFN	1SVR 450 201 R1200	CM-EFS	1SVR 430 750 R0400

Type old	Order code old	Type new	Ordercode new
----------	----------------	----------	---------------

C552.01	1SAR 421 010 R0001	CM-ESS.1	1SVR 430 830 R0300
C552.01	1SAR 421 010 R0002	CM-ESS.1	1SVR 430 830 R0300
C552.01	1SAR 421 010 R0004	CM-ESS.1	1SVR 430 831 R0300
C552.01	1SAR 421 010 R0005	CM-ESS.1	1SVR 430 831 R1300
C552.02	1SAR 422 010 R0001	CM-ESS.1	1SVR 430 830 R0300
C552.02	1SAR 422 010 R0002	CM-ESS.1	1SVR 430 830 R0300
C552.02	1SAR 422 010 R0004	CM-ESS.1	1SVR 430 831 R0300
C552.02	1SAR 422 010 R0005	CM-ESS.1	1SVR 430 831 R1300
C553	1SAR 425 010 R0008	CM-EFS	1SVR 430 750 R0400
C553	1SAR 425 010 R0009	CM-EFS	1SVR 430 750 R0400

Three-phase monitors for over- and undervoltage

CM-PFN	1SVR 450 311 R0400	CM-PSS	1SVR 430 784 R2300
CM-PFN	1SVR 450 312 R0400	CM-PSS	1SVR 430 784 R2300
CM-PFN	1SVR 450 311 R0500	CM-PSS	1SVR 430 784 R3300
CM-PFN	1SVR 450 312 R0500	CM-PSS	1SVR 430 784 R3300
CM-PVN	1SVR 450 300 R1200	CM-PVS	1SVR 430 794 R1300
CM-PVN	1SVR 450 301 R1200	CM-PVS	1SVR 430 794 R1300
CM-PVN	1SVR 450 300 R1500	CM-PVS	1SVR 430 794 R3300
CM-PVN	1SVR 450 301 R1500	CM-PVS	1SVR 430 794 R3300
CM-PVN	1SVR 450 302 R1500	CM-PVS	1SVR 430 794 R3300
CM-PVN	1SVR 450 300 R1700*	-	-
CM-PVN	1SVR 450 302 R1700*	-	-

Three-phase monitors for unbalance

CM-ASS	1SVR 430 864 R1100	CM-PAS	1SVR 430 774 R1300
CM-ASS	1SVR 430 864 R3100	CM-PAS	1SVR 430 774 R3300
CM-ASS	1SVR 430 865 R1100	CM-PAS	1SVR 430 774 R1300
CM-ASS	1SVR 430 865 R3100	CM-PAS	1SVR 430 774 R3300
CM-ASN	1SVR 450 320 R0200	CM-PAS	1SVR 430 774 R1300
CM-ASN	1SVR 450 321 R0200	CM-PAS	1SVR 430 774 R1300
CM-ASN	1SVR 450 322 R0200	CM-PAS	1SVR 430 774 R1300
CM-ASN	1SVR 450 421 R0200	CM-PAS	1SVR 430 774 R1300
CM-ASN	1SVR 450 320 R0500	CM-PAS	1SVR 430 774 R3300
CM-ASN	1SVR 450 321 R0500	CM-PAS	1SVR 430 774 R3300
CM-ASN	1SVR 450 322 R0500	CM-PAS	1SVR 430 774 R3300
CM-ASN	1SVR 450 422 R0500	CM-PAS	1SVR 430 774 R3300
CM-ASN	1SVR 450 423 R0600	CM-PAS	1SVR 430 774 R3300
CM-ASN	1SVR 450 320 R0700	CM-PAS	1SVR 430 774 R3300
CM-ASN	1SVR 450 321 R0700	CM-PAS	1SVR 430 774 R3300
CM-ASN	1SVR 450 322 R0700	CM-PAS	1SVR 430 774 R3300
CM-ASN	1SVR 450 932 R0100	CM-PAS	1SVR 430 774 R3300
CM-ASN	1SVR 450 424 R0700	CM-PAS	1SVR 430 774 R3300
CM-ASN	1SVR 450 426 R0800*	-	-

* still available