

Product	Followed by	May be followed by	May be followed by	UL	UL standard	CSA
OESA-F30	J6, JT6, T3 or T6	-S	A	E101914 (Listed)	UL98	LR58077 (Certified)
OESA-F30	C6	-	-	-	-	LR58077 (Certified)
OESA-F60	J6, JT6, T3 or T6	-S	A	E101914 (Listed)	UL98	LR58077 (Certified)
OESA-F60	C6	-	-	-	-	LR58077 (Certified)
OESA-F100	J6, JT6, T3 or T6	-S	A	E101914 (Listed)	UL98	LR58077 (Certified)
OESA-F100	C6	-	-	-	-	LR58077 (Certified)
OESA-F200	J6, JT6, T3 or T6	P or -S	-	E101914 (Listed)	UL98	LR58077 (Certified)
OESA-F200	C6	-	-	-	-	LR58077 (Certified)
OESA-F400	J6, JT6, T3 or T6	P or -S	-	E101914 (Listed)	UL98	LR58077 (Certified)
OESA-F400	C6	-	-	-	-	LR58077 (Certified)
OESA-F600	J6, JT6, T6 or T3	P	-	E101914 (Listed)	UL98	LR58077 (Certified)
OESA-F600	C6	-	-	-	-	LR58077 (Certified)
OESA-F800	L6 or T6	P	-	E101914 (Listed)	UL98	LR58077 (Certified)
OES200J	2, 3, 4, 11, 12, 13, 21, 22 or 31	P or -S	-	E101914 (Listed)	UL98	LR58077 (Certified)
OES400J	2, 3, 4, 11, 12, 13, 21, 22 or 31	P or -S	-	E101914 (Listed)	UL98	LR58077 (Certified)
OES600J	2, 3, 4, 11, 12, 13, 21, 22 or 31	P	-	E101914 (Listed)	UL98	LR58077 (Certified)
OES800L	2, 3, 4, 11, 12, 13, 21, 22 or 31	P	-	E101914 (Listed)	UL98	LR58077 (Certified)

25.11.2002