

Tmax

DOC. N.° 1SDH000436R0825 - L5663

FC Cu - Terminali anteriori per cavi in rame T4-T5 fisso
 FC Cu - Front terminals for copper cables T4-T5 fixed
 FC Cu - Vorderseitige Anschlüsse für Kupferkabel T4-T5 fest
 FC Cu - Prises avant pour câbles en cuivre T4-T5 fixe
 FC Cu - Terminales frontales para cables de cobre T4-T5 fijo
 FC Cu - 铜电缆前接线端子 T4-T5 固定式

T4		T5	
III	3(6) 3(6)	III	3(6) 3(6)
IV	4(8) 4(8)	IV	4(8) 4(8)

T5	
III	IV
1(2)	1(2)
3(6)	4(8)
3(6)	4(8)
3(6)	4(8)
3(6)	4(8)

A T4


min 20
 $\varnothing \max 18$
 $\ominus 10 \text{ Nm}$

B T5

NO! 11 13 180° OK 13 11
 min 26
 $\varnothing \max 24$
 $\ominus 25 \text{ Nm}$

C


1 2



T4	MAX 最大	185 mm ²	MAX 最大	120 mm ²
	MIN 最小	2,5 mm ²	MIN 最小	2,5 mm ²
T5	MAX 最大	300 mm ²	MAX 最大	240 mm ²
	MIN 最小	16 mm ²	MIN 最小	16 mm ²


D

T5




E

T5



F

3



T5	MAX 最大	240 mm ²
	MIN 最小	120 mm ²

ABB

<http://www.abb.com>