







# Tmax

DOC. N.° Rh0012808 - L6115

FC Cu - Terminali per cavi T2-T3 fisso/parte fissa di rimovibile.  
 FC Cu - Terminals for cables T2-T3 Fixed/plug-in fixed part.  
 FC Cu - Anschlüsse für Kabel T2-T3 fest/ausfahrbarer festes teil.  
 FC Cu - Prises pour câbles T2-T3 fixe/partie fixe de débrochable.  
 FC Cu - Terminales para cables T2-T3 fijo/parte fija de enchufable.  
 FC Cu - 铜电缆前接线端子 T2-T3 固定式/插入式的固定部件

	T2 III	T2 IV	T3 III	T3 IV
	3 (6)	4 (8)	-	-
	3 (6)	4 (8)	-	-
	-	-	3 (6)	4 (8)
	-	-	3 (6)	4 (8)



C

T2



MAX  
最大

95 mm<sup>2</sup>

70 mm<sup>2</sup>

MIN  
最小

1 mm<sup>2</sup>

1 mm<sup>2</sup>

T3



MAX  
最大

185 mm<sup>2</sup>

150 mm<sup>2</sup>

MIN  
最小

6 mm<sup>2</sup>

6 mm<sup>2</sup>