

Service suitcases for ABB drives

Product specific drive service suitcases guarantee access to vital spare parts whenever and wherever they are needed. No upfront capital expenditures are required if the suitcase is supplied as a vendor managed Inventory Access solution.

Use of a service suitcase on-site may substantially shorten the leadtime to troubleshoot a drive failure. It also reduces the time spent for locating the necessary parts and the service material carrying costs associated with traditional inventory maintenance.



The drives service suitcase has been developed to guarantee on-site service personnel's access to critical spare parts.

Service notes

Benefits

- Shortened response time to start the drive
- Guaranteed access to genuine, factory-certified ABB parts
- Compact set of spare parts that is easy to use
- Robust construction to protect electronics during transportation
- Lower long-term ownership costs

Service provides

- Complete set of spare parts fitted into a compact suitcase
- ESD protection for parts
- Systematic replacement routine for used parts
- Vendor managed parts maintained at your site (Inventory Access option)

Product Lifecycle Services

- Installation & Commissioning
- Training
- Support & Remote Services
- Spare Parts & Repairs
- Maintenance & Field Services
- Migration & Retrofits
- Optimization





SP18 EN REVG 2008

Service notes

Table of suitcases

Main code	Type	Power range Nominal P [kW]	Output current 10% overload I [A]	Main supply voltage U [V]	Frame size
ACS600					
ACS601A	ACS601-0005-3_0060-5	3 - 45	8,4 - 72	380 - 500	R2 - R5
ACS601B	ACS601-0060-3_0400-5	45 - 315	98 - 506	380 - 500	R6 - R9
ACS600XTA	ACS607-0400-3_0760-5	110 - 630	238 - 961	380 - 500	R8 - 2xR9
ACS601C	ACS601-0009-6_0120-6	5,5 - 90	8,4 - 116	690	R3 - R7
ACS600XTB	ACS607-0140-6_0760-6	110 - 630	140 - 734	690	R8 - 2xR9
ACS800					
ACS800-01	ACS800-0x-0040-3_0255-5	30 - 200	69 - 285	380 - 500	R5 - R6
ACS800-02	ACS800-0x-0140-3_0610-5	110 - 500	202 - 704	380 - 500	R7 - R8
ACS800-01-7	ACS800-0x-0050-7_0205-7	37 - 160	46 - 180	690	R5 - R6
ACS800-02-7	ACS800-0x-0140-7_0610-7	110 - 500	134 - 560	690	R7 - R8
ACS800DSU	ACS800-307/507-0200-3_4540-7	183 - 4202	286 - 3796	380 - 690	D3 - 5xD4
ACS800-11	ACS800-11-0016-3_0100-7	15 - 75	32 - 88	380 - 690	R5 - R6
ACS800-67A	ACS800-67	450 - 900	467 - 914	690	R8i - 2xR8i
ACS800-67B	ACS800-67+V991	450 - 900	467 - 914	690	R8i - 2xR8i
ACS800-104A	ACS800-104R8i	132 - 2900	240 - 3830	380 - 500	R8i - 6xR8i
ACS800-104B	ACS800-104R8i+V991	132 - 2900	240 - 3830	380 - 500	R8i - 6xR8i
ACS800-104C	ACS800-104R8i-7	160 - 5400	163 - 5319	690	R8i - 12xR8i
ACS800-104D	ACS800-104R8i-7+V991	160 - 5400	163 - 5319	690	R8i - 12xR8i
ACS550					
ACS550-01	ACS550-01-06A9-4_290A-4	3 - 160	6,9 - 290	380 - 480	R1 - R6
ACS550-02	ACS550-02-196A-4_645A-4	110 - 355	196 - 645	380 - 480	R7 - R8
ACSM1					
42000402	ACSM1-04AX-02A5-4_090A-4	0,75-45	-	380-480	A-D
DCS400					
DCS400 SUITCASE	Suitcase DCS400	9 - 522		400 - 500	A1 - A4



ABB Oy
Product Support
PO Box 116
FIN-00381 Helsinki, Finland
Tel: +358 10 22 11
Fax: +358 10 22 26800
www.abb.com/drives
e-mail: sales.productsupport@fi.abb.com

ABB Automation GmbH
Service Export
Kallstadter Str.1
D-68309 Mannheim, Germany
Tel.: +49 621 381 1579
Fax: +49 621 381 1585
www.abb.com/drives