

## M3AA 090 LD

### Motor Dimension Print

Motor Type :


M3AA 090 LD IMB34 FT-85

Document N° :

A1.4917 / 3D A2.5014

Description :

Motor foot and flange mounted special (2-pieces) / Motor patas y brida esp. (2 piezas) IM2101



Unit : Discrete Automation & Motion - Fábrica Motores

Issued by : EMD/ G.Gállego

Replaces : To date 2008-03-27

Date : 2011-03-02

Approved by : EMD/ G.Blanes

Replaced by :

Asea Brown Boveri, S.A.

Customer Reference :

**ABB**