






DRAWING NUMBER
D 2501 8003-020



OT1200U12		
600VAC	1200A	3-Pole
Non-Fused Open Type Switch		
Rotary operated		
cULus Listed, 97C2		
Open Type Switch		
UL File #101914		
CSA Certified, File #58077		
Short Circuit Rating at 600VAC		
KA	Fuse/A	Fuse class
100	1200	L
50		Circuit Breaker

Accessories:

Operating Handle
 OHR200U12P - Type 1, 3R, 12
 OHR200L12P - Type 1, 3R, 4, 4X, 12
 YASDA-9 - Type 4X
 Ref: drawing D 2301 8001-001
 for pistol handle dimensions and
 installation details.

Terminal Lug Kits
 O7XA-1200 - 6 Lugs
 Wire Range:
 (4) #2 AWG - 600Kcmil
 AL7CU, UL Recognized

Operating Shaft - Max. encl. depth
 OXP12X280 - 15.20 in.
 OXP12X325 - 17.00 in.
 OXP12X395 - 19.70 in.
 OXP12X465 - 22.40 in.
 OXP12X535 - 25.20 in.

Auxiliary Contacts
 OA1G10 - 1n.o.
 OA3G01 - 1n.c.

THIS DRAWING IS THE PROPERTY OF ABB Inc. AND CONTAINS PROPRIETARY AND CONFIDENTIAL INFORMATION WHICH MUST NOT BE OR REPRODUCED OR DISCLOSED OTHER THAN EXPRESSLY AUTHORIZED BY ABB Inc.

ABB Inc.

DATE: 11/3/11
 DRAWN: F. GARCIA
 CHK'D: A
 PROJECT NO.:
 SHEET 1 OF 1

REV. A
 TITLE: OT1200U12
 3-Pole Non-Fused Open Type Switch
 DRAWING NUMBER: D 2501 8003-020

REV. LET.	REVISIONS	DATE	REV OR APPD BY