



DRAWING NUMBER
D 2501 8014-026



Short Circuit Rating at 600VAC	
KA	Fuse/A
200	1200
	Fuse class
	L

OS1200L40
600VAC 1200A 4-Pole
Class L Fused Open
Type Switch
Rotary operated
Cullus Listed, 97C2
Open Type Switch
UL File #E101914

Accessories:

Operating Handle
OHB200J12P - Type 1, 3R, 12
OHB200L12P - Type 1, 3R, 4, 4X, 12
Ref. drawing D 2301 8001-014 for
t-style grip handle dimensions and
installation details.

Terminal Lug Kits
OZXA-1200 - 8 lugs
OZXA-1200/3 - 4 lugs
Wire Range:
(4) #2 AWG - 600kcmil
AL7Cu, UL Listed

Operating Shaft - Max. encl. depth
OXP12X280 - 15.20 in.
OXP12X325 - 17.00 in.
OXP12X395 - 19.70 in.
OXP12X465 - 22.40 in.
OXP12X355 - 25.20 in.

Auxiliary Contacts
OA1G10 - 1n.o.
OA3G01 - 1n.c.
OEA28 - Module for contacts

CUST / SHOP

DO NOT SCALE DRAWING		THIS DRAWING IS THE PROPERTY OF ABB Inc. AND CONTAINS PROPRIETARY AND CONFIDENTIAL INFORMATION WHICH MUST NOT BE OR REPRODUCED, COPIED, OR TRANSMITTED IN ANY FORM OR BY ANY MEANS WITHOUT THE EXPRESS AUTHORIZATION BY ABB Inc.	
SCALE 5/32"	DIMENSIONS ARE IN INCHES	DATE	11/3/11
Material:	Finish:	DRAWN	F. GARCIA
STANDARD TOLERANCES		CHK'D	
2 PL DEC. ±.030	3 PL DEC. ±.030	APPR'D	
ANGLES ±1°		SHEET	1 OF 1
REV. LET.	REVISIONS	DATE	REV. TITLE
			A OS1200L40
			A 4-POLE FUSIBLE
			A OPEN TYPE SWITCH
			D 2501 8014-026