

DRAWING NUMBER  
D 2501 8004-015

OT800U04  
600VAC 800A 4-Pole  
Non-Fused Open Type Switch  
Rotary operated

cULus Listed, 97C2  
Open Type Switch  
UL File #101914  
CSA Certified, File #58077

Short Circuit Rating at 600VAC		
KA	Fuse/A	Fuse class
100	1200	L
50	Circuit Breaker	

3-phase HP Ratings		
VAC	240	480 600
HP	250	500 600






Accessories:


**Operating Handle**  
 OHB200J12P - Type 1, 3R, 12  
 OHB200L12P - Type 1, 3R, 4, 4X, 12  
 YASDA-9 - Type 4X  
 Ref. drawing D 2301 8001-001  
 for pistol handle dimensions and  
 installation details.

**Terminal Lug Kits**  
 OZXA-1200 - 8 Lugs  
 Wire Range:  
 (4) #2 AWC - 600kcmil  
 AL7CU, UL Recognized

**Operating Shaft - Max. encl. depth**  
 OXP12X280 - 15.20 in.  
 OXP12X325 - 17.00 in.  
 OXP12X395 - 19.70 in.  
 OXP12X465 - 22.40 in.  
 OXP12X535 - 25.20 in.

**Auxiliary Contacts**  
 DATG10 - 1n.o.  
 OASG01 - 1n.c.



REV. LET.	REVISIONS	DATE	REV OR APPD BY	THIS DRAWING IS THE PROPERTY OF ABB Inc. AND CONTAINS PROPRIETARY AND CONFIDENTIAL INFORMATION WHICH MUST NOT BE OR REPRODUCED OR DISCLOSED OTHER THAN EXPRESSLY AUTHORIZED BY ABB Inc.		DATE	REV.	TITLE
		14/3/11				A	OT800U04	
		F. GARCIA				A	4-Pole Non-Fused Open Type Switch	
		PROJECT NO.					DRAWING NUMBER	
		SHEET 1 OF 1		A	D 2501 8004-015			