

DRAWING NUMBER
D 2501 8004-017

OT800U22
600VAC 800A 4-Pole
Non-Fused Open Type Switch
Rotary operated

cULus Listed, 97C2
Open Type Switch
UL File #101914
CSA Certified, File #58077

Short Circuit Rating at 600VAC

KA	Fuse/A	Fuse class
100	1200	L
50		Circuit Breaker

3-phase HP Ratings		
VAC	240	480 600
HP	250	500 600



Accessories:

Operating Handle
OHB200J12P - Type 1, 3R, 12
OHB200L12P - Type 1, 3R, 4, 4X, 12
YASDA-9 - Type 4X
Ref. drawing D 2301 8001-001
for pistol handle dimensions and
installation details.

Terminal Lug Kits
OZXA-1200 - 8 Lugs
Wire Range:
(4) #2 AWC - 600kcmil
AL7CU, UL Recognized

Operating Shaft - Max. encl. depth
OXP12X280 - 15.20 in.
OXP12X325 - 17.00 in.
OXP12X395 - 19.70 in.
OXP12X465 - 22.40 in.
OXP12X535 - 25.20 in.

Auxiliary Contacts
DATG10 - 1n.o.
OASG01 - 1n.c.



REV.	LET.	REVISIONS	DATE	REV OR APPD BY	THIS DRAWING IS THE PROPERTY OF ABB Inc. AND CONTAINS PROPRIETARY AND CONFIDENTIAL INFORMATION WHICH MUST NOT BE OR REPRODUCED OR DISCLOSED OTHER THAN EXPRESSLY AUTHORIZED BY ABB Inc.	ABB Inc.	DATE 14/3/11	REV. A	TITLE 4-Pole Non-Fused Open Type Switch
							DRAWN F. GARCIA	SIZE A	DRAWING NUMBER D 2501 8004-017
							PROJECT NO.		
							CHEK'D		
							SHEET 1 OF 1		