

DRAWING NUMBER  
D 2501 8002-008

OT1200U02  
600VAC 1200A 2-Pole  
Non-Fused Open Type Switch  
Rotary operated

cULus Listed, 97C2  
Open Type Switch  
UL File #101914  
CSA Certified, File #58077

Short Circuit Rating at 600VAC		
KA	Fuse/A	Fuse class
100	1200	J
50		Circuit Breaker





Accessories:


**Operating Handle**  
OHB200J12P - Type 1, 3R, 12  
OHB200L12P - Type 1, 3R, 4, 4X, 12  
YASDA-9 - Type 4X  
Ref: drawing D 2301 8001-001  
for pistol handle dimensions and  
installation details.

**Terminal Lug Kits**  
OZXA-1200 - 6 Lugs  
Wire Range:  
(4) #2 AWG - 600kcmil  
AL7Cu, UL Recognized

**Operating Shaft - Max. encl. depth**  
OXP12X280 - 15.20 in.  
OXP12X325 - 17.00 in.  
OXP12X395 - 19.70 in.  
OXP12X465 - 22.40 in.  
OXP12X535 - 25.20 in.

**Auxiliary Contacts**  
OA1G10 - 1n.o.  
OA3G01 - 1n.c.



REV. LET.	REVISIONS	DATE	REV OR APPD BY	<p>THIS DRAWING IS THE PROPERTY OF ABB Inc. AND CONTAINS PROPRIETARY AND CONFIDENTIAL INFORMATION WHICH MUST NOT BE OR REPRODUCED OR OTHERWISE USED IN ANY MANNER WITHOUT THE EXPRESS AUTHORIZATION BY ABB Inc.</p> 	DATE 4/28/11	REV. A	TITLE OT1200U02
					DRAWN TD		
					CHK'D		
					PROJECT NO.		
				SHEET 1 OF 1		SIZE A	DRAWING NUMBER D 2501 8002-008