


DRAWING NUMBER
D 2501 8014-027



Short Circuit Rating at 600VAC		
KA	Fuse/A	Fuse class
200	1200	L

OS1200L13
600VAC 1200A 4-Pole
Class L Fused Open
Type Switch
Rotary operated
cullus Listed, 97C2
Open Type Switch
UL File #E101914

Accessories:

Operating Handle
OHB200J12P - Type 1, 3R, 12
OHB200L12P - Type 1, 3R, 4, 4X, 12
Ref. drawing D 2301 8001-014 for
t-style grip handle dimensions and
installation details.

Terminal Lug Kits
OZXA-1200 - 8 lugs
OZXA-1200/3 - 4 lugs
Wire Range:
(4) #2 AWG - 600kcmil
AL7Cu, UL Listed

Operating Shaft - Max. encl. depth
OXPI2X280 - 15.20 in.
OXPI2X325 - 17.00 in.
OXPI2X395 - 19.70 in.
OXPI2X465 - 22.40 in.
OXPI2X355 - 25.20 in.

Auxiliary Contacts
OA1G10 - 1n.o.
OA3G01 - 1n.c.
OEA28 - Module for contacts

CUST / SHOP

REV.	LET.	REVISIONS	DATE	REV OR APPD BY	STANDARD TOLERANCES	ANGLES
					2 PL DEC. ±.030	±1°
					3 PL DEC. ±.030	±1°

DO NOT SCALE DRAWING	
SCALE 5/32"	DIMENSIONS ARE IN INCHES
Material:	
Finish:	

THIS DRAWING IS THE PROPERTY OF ABB Inc. AND CONTAINS PROPRIETARY AND CONFIDENTIAL INFORMATION WHICH MUST NOT BE OR REPRODUCED, COPIED, DULICATED, USED OR TRANSMITTED IN ANY MANNER WITHOUT THE EXPRESS AUTHORIZATION BY ABB Inc.	
ABB Inc.	
DATE 11/3/11	
DRAWN F. GARCIA	
CHK'D	
APPR'D	
SHEET 1 OF 1	
REV. A	TITLE OS1200L13
SIZE A	4-POLE FUSIBLE OPEN TYPE SWITCH
	DRAWING NUMBER D 2501 8014-027