



中国国家强制性产品认证证书

证书编号: 2008010304269002

委托人名称、地址

ABB-ENTRELEC Division Control
10 rue Ampere Z. I. BP114 69685 Chassieu cedex France

生产者(制造商)名称、地址

ABB-ENTRELEC Division Control
10 rue Ampere Z. I. BP114 69685 Chassieu cedex France

生产企业名称、地址

ABB-ENTRELEC Division Control
10 rue Ampere Z. I. BP114 69685 Chassieu cedex France

产品名称和系列、规格、型号

接触器

AF50-30, AF63-30, AF75-30, AF50-40, AF75-22, AF75-40; 详见参数附件

产品标准和技术要求

GB 14048.4-2003

上述产品符合强制性产品认证实施规则
CNCA-01C-011:2007的要求, 特发此证。

发证日期: 2010年04月29日

有效期至: 2015年04月29日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书, 证书首次颁发日期: 2008年03月19日

本证书的相关信息可通过国家认监委网站www.cnca.gov.cn查询



主任:

中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>



Q 0249898



中国国家强制性产品认证证书

附录:

第 1 页 共 4 页

证书编号: 2008010304269002

纸号: 249898

AF50-30, AF63-30, AF75-30, AF50-40, AF75-22, AF75-40

AF50-30:

Ith: 100A;

AC-3, AC-4:

$U_e \leq 240V$ $I_e = 53A$;

$240V < U_e \leq 415V$ $I_e = 50A$;

$415V < U_e \leq 500V$ $I_e = 45A$;

$500V < U_e \leq 690V$ $I_e = 35A$;

AC-8a: $U_e = 400V$ $I_e = 63A$;

AF63-30:

Ith: 125A;

AC-3, AC-4:

$U_e \leq 440V$ $I_e = 65A$;

$440V < U_e \leq 500V$ $I_e = 55A$;

$500V < U_e \leq 690V$ $I_e = 43A$;

AC-8a: $U_e = 400V$ $I_e = 85A$;

AF75-30:

Ith: 125A;

AC-3, AC-4:

注: 此附录与证书同时使用时有效。



主任:

中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>





中国国家强制性产品认证证书

附录:

第 2 页 共 4 页

证书编号: 2008010304269002

纸号: 249898

$U_e \leq 400V$ $I_e = 75A$;
 $400V < U_e \leq 415V$ $I_e = 75A$;
 $415V < U_e \leq 440V$ $I_e = 70A$;
 $440V < U_e \leq 500V$ $I_e = 65A$;
 $500V < U_e \leq 690V$ $I_e = 46A$;
AC-8a: $U_e = 400V$ $I_e = 95A$;

AF50-40:
 $I_{th} = 100A$;
AC-1:
 $U_e = 690V$ $I_e = 100A$;
AC-3, AC-4:
 $U_e \leq 240V$ $I_e = 53A$;
 $240V < U_e \leq 415V$ $I_e = 50A$;
 $415V < U_e \leq 500V$ $I_e = 45A$;
 $500V < U_e \leq 690V$ $I_e = 35A$;

AF75-22:
 $I_{th} = 125A$;
AC-1: $U_e = 690V$ $I_e = 125A$;

注: 此附录与证书同时使用时有效。



主任:

中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>





中国国家强制性产品认证证书

附录:

第 3 页 共 4 页

证书编号: 2008010304269002

纸号: 249898

AF75-40:

Ith: 125A;

AC-1: $U_e=690V$ $I_e=125A$;

AC-3, AC-4: $U_e \leq 415V$ $I_e=75A$;

$415V < U_e \leq 440V$ $I_e=70A$;

$440V < U_e \leq 500V$ $I_e=65A$;

$500V < U_e \leq 690V$ $I_e=46A$;

Us: 100-250V 50/60Hz/DC, 48-130V 50/60Hz/DC, 20-60V DC;
3P, 4P

注: 此附录与证书同时使用时有效。



主任:

中国质量认证中心

中国·北京·南四环西路188号9区 100070

<http://www.cqc.com.cn>





中国国家强制性产品认证证书

附录:

第 4 页 共 4 页

证书编号: 2008010304269002

纸号: 249898

型号的解释:

AF	-50-	40	-00
I	II	III	IV

I: Product series

II: Basic type AF50,AF63,AF75

III: Contacts of the contactor (main poles):AFX-30;-40; -22

30: 3NO

40: 4NO

22: 2NO+2NC

IV: No. of auxiliary contact :00:0NC+0NO

注: 此附录与证书同时使用时有效。



主任:

中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

No. : 2008010304269002

NAME AND ADDRESS OF THE APPLICANT

ABB-ENTRELEC Division Control
10 rue Ampere Z. I. BP114 69685 Chassieu cedex France

NAME AND ADDRESS OF THE MANUFACTURER

ABB-ENTRELEC Division Control
10 rue Ampere Z. I. BP114 69685 Chassieu cedex France

NAME AND ADDRESS OF THE FACTORY

ABB-ENTRELEC Division Control
10 rue Ampere Z. I. BP114 69685 Chassieu cedex France

NAME, MODEL AND SPECIFICATION

Contactor

AF50-30, AF63-30, AF75-30, AF50-40, AF75-22, AF75-40; See the Appendix

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB 14048.4-2003

This is to certify that the above mentioned products have met the requirements of implementation rules for compulsory certification (REF NO. CNCA-01C-011:2007).

Date of issue: Apr. 29, 2010 Date of expiry: Apr. 29, 2015

Validity of this certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original certification: Mar. 19, 2008

This certificate can be verified through CNCA's website: www.cnca.gov.cn



President:

Wang Kejiao

CHINA QUALITY CERTIFICATION CENTRE

Section 9, No. 188, Nansihuan Xilu, Beijing 100070 P.R. China

<http://www.cqc.com.cn>



Q 0249898