



中国国家强制性产品认证证书

证书编号: 2002010304007860

委托人名称、地址

ABB AB, Cewe-Control
SE-721 61 Vasteras, Sweden

生产者(制造商)名称、地址

ABB AB, Cewe-Control
SE-721 61 Vasteras, Sweden

生产企业名称、地址

ABB AB, Cewe-Control
SE-721 61 Vasteras, Sweden

产品名称和系列、规格、型号

接触器

AF95, AF95... RT, AF95B... RT, AF110, AF110... RT, AF110B... RT; 详见参数附件

产品标准和技术要求

GB 14048.4-2003

上述产品符合强制性产品认证实施规则
CNCA-01C-011: 2007的要求, 特发此证。

发证日期: 2010年11月03日

有效期至: 2015年11月03日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书, 证书首次颁发日期: 2002年07月16日

本证书的相关信息可通过国家认监委网站www.cnca.gov.cn查询



主任:

中国质量认证中心

中国·北京·南四环西路188号9区 100070

<http://www.cqc.com.cn>



Q 0305765



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

No. : 2002010304007860

NAME AND ADDRESS OF THE APPLICANT

ABB AB, Cewe-Control
SE-721 61 Vasteras, Sweden

NAME AND ADDRESS OF THE MANUFACTURER

ABB AB, Cewe-Control
SE-721 61 Vasteras, Sweden

NAME AND ADDRESS OF THE FACTORY

ABB AB, Cewe-Control
SE-721 61 Vasteras, Sweden

NAME, MODEL AND SPECIFICATION

Contactor

AF95, AF95... RT, AF95B... RT, AF110, AF110... RT, AF110B... RT; See the Appendix

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB 14048.4-2003

This is to certify that the above mentioned products have met the requirements of implementation rules for compulsory certification (REF NO. CNCA-01C-011:2007).

Date of issue: Nov. 03, 2010 Date of expiry: Nov. 03, 2015

Validity of this certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original certification: Jul. 16, 2002

This certificate can be verified through CNCA's website: www.cnca.gov.cn



President:

Wang Kejiao

CHINA QUALITY CERTIFICATION CENTRE

Section 9, No. 188, Nansihuan Xilu, Beijing 100070 P.R. China

<http://www.cqc.com.cn>



Q 0305765



中国国家强制性产品认证证书

附录:

第 1 页 共 2 页

证书编号: 2002010304007860

纸号: 305765

AF95, AF95...RT, AF95B...RT, AF110, AF110...RT, AF110B...RT

AF95, AF95...RT, AF95B...RT:

Ith=145A

AC-1:Ue/Ie: 415/690V/1000V/145A;

AC-3:Ue/Ie: 220-240-380-400-415V/96A, 660-690V/65A,1000V/30A;

AF110, AF110...RT, AF110B-RT:

Ith=160A

AC-1:Ue/Ie: 415/690/1000V/160A;

AC-3:Ue/Ie: 220-240-380-400-415V/110A, 660-690V/82A,1000V/30A;

Us: 48-130V, 100-250V AC/DC;

3P

配用的辅助触头:

CAL18-11/CAL18B-11RT:

Ith=16A

AC-15:Ue/Ie: 24-127V/6A,220-240V/4A,280-440V/3A,500-690V/2A;

DC-13:Ue/Ie: 24V/6A,48V/2.8A,72V/1A,125V/0.55A,250V/0.3A

注: 此附录与证书同时使用时有效。



主任:

中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>





中国国家强制性产品认证证书

附录:

第 2 页 共 2 页

证书编号: 2002010304007860

纸号: 305765

型号的解释:

AF 110 B - 30 - 11 RT
1 2 3 4 5 6

1. Product series code
2. Size code
3. B = smoke & fire approval, blank= normal product
4. Main contacts: NO& NC quantity 30: 3 NO+ 0 NC.
5. Auxiliary contacts: NO&NC quantity 11: 1NO+1NC
6. RT: Ring Terminals blank: normal terminals

注: 此附录与证书同时使用时有效。



主任:

中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>

