
















Apparatus:		XLP 000 3-POLE 100A	XLP 00 3-POLE 160A	SLP 1 3-POLE 250A	SLP 2 3-POLE 400A	SLP 3 3-POLE 630A	SLP- 3-PO 250
1	Switch	1SEP 201428R0001	1SEP 101890R002	NHPL 045211R0001	NHPL 045311R0001	NHPL 045321R0001	NHPL 139740R0001
Including: Accessories:		6 Cage Clamps (6 CC)	6 Bridge Clamps (6 BC)	6 ABB Clamps + 3 bolts / washers	6 ABB Clamps + 3 bolts / washers	6 ABB Clamps + 3 bolts / washers	1)
2	Front frame for 1 apparatus	1SEP 407741R0001	1SEP 407792R0001	NHPL 045251R0001	NHPL 045351R0001	NHPL 045351 R0001	
3	Front frame for 2 apparatus	1SEP 407741R0002	1SEP 407792R0002				
4	Front frame for 3 apparatus	1SEP 407741R0003	1SEP 407792R0003				
5	Micro auxiliary switch	1SEP 407742R0001	1SEP 407742R0001				
6	Auxiliary switch NC		1SEP 407742R0002				
7	Auxiliary switch NO		1SEP 407742R0003				
8	Padlock device		1SEP 407786R0001				
9	Cable shroud		1SEP 407793R0001				
10	Front fixing device compl.			NHPL 045252R0001	NHPL 045352R0001	NHPL 045352R0001	
11	Front fixing device without steel brackets			NHPL 045255R0001	NHPL 045355R0001	NHPL 045355R0001	
12	Front fixing bracket and front frame		NHP 403634R0001				NH 403635R0001
13	DIN Rail mounting device	1SEP 407740R0001	NHPL 045158R0001				
14	Cover IP 30			NHP 139279P0001			NH 139763R0001
15	Auxiliary contact b			NHPL 045270R0001	NHPL 045270R0001	NHPL 045270R0001	NHPL 045270R0001
16	Auxiliary contact h			NHPL 045253R0001	NHPL 045353R0001	NHPL 045353R0001	
17	Electronic fuse- monitoring kit		1SEP 304233R0001				
18	Cover with fuse- surveillance M611			NHPL 045254R0001	NHPL 045354R0001	NHPL 045354R0001	NHPL 045254R0001
19	Bridge Clamp 1,5-50 mm² Al/Cu		1SEP 407733R0001				
20	Sing. Pris. Clamp 1,5-70 mm² Al/Cu		1SEP 407732R0001				
21	Triple Clamp 1,0-10 mm² Al/Cu		1SEP 407787R0001				
22	Feeding Clamp 25-95 mm² Al/Cu		1SEP 407811R0001				
23	JM Single cable clamps Al/Cu						NH 403628R0001 3 pcs.
24	JM Double cable clamps Al/Cu						NH 403631R0001 3 pcs.
25	ABB Single cable clamps Al/Cu						NH 403627R0001 3 pcs.
26	KP Single cable clamps, Al/Cu						
27	KP Double cable clamps, Al/Cu						
28	Bolts for cable lug and busbars connection, Al/Cu		NHP 400940 R0006 3 pcs.				NH 403625R0001 3 pcs.



EasyLine

A new generation designed for you




ABB Building Technologies




XLP 000:
An optimal solution up to 100 A


- Compact design for NH 00 compact fuses up to 100A
- Modern integrated cable clamps for 1,5 - 35 mm² cables
- Integrated cable shrouds IP 20
- Snap on for DIN rail mounting
- Front frames for 1 - 3 apparatus
- Micro auxiliary switches, 1 or 2 pcs
- Sealing facility



Front frames for 1-3 apparatus



Snap on for
DIN rail mounting



Sealing facility

Voltage measurement

**XLP 00:
Optimal design and technique...
giving even more possibilities by accessories**

- New electronic fuse monitoring
- Micro auxilliary switches, 1 or 2 pcs
- Auxilliary switches, 1 NO or 1 NC acc. to IEC 60947-5-1
- Cable shrouds
- Wide range of cable terminal clamps
- Front frames for 1 - 3 apparatus

- Kit for DIN rail mounting
- Different types of plug – in busbar adapters
- Padlocking facility
- Sealing facility



Padlocking and Sealing facilities



Micro auxiliary switch on the sides.
Auxiliary switch NO or NC in the front



Electronic fuse monitoring showing detail for remote signaling



Bridge Clamp (BC) 1,5 - 50 mm²



Triple Clamp (TC) 1,0 - 10 mm²



Bolts for cable lugs (M)



Single Prisme Clamps (SPC) 1,5 - 70 mm²

