



中国国家强制性产品认证证书

证书编号: 2005010302143043

委托人名称、地址

ABB Oy, Low Voltage Products
Muottitie 2A, P.O.Box 622, FIN-65101 VAASA, 芬兰

生产者(制造商)名称、地址

ABB Oy, Low Voltage Products
Muottitie 2A, P.O.Box 622, FIN-65101 VAASA, 芬兰

生产企业名称、地址

ABB Oy, Low Voltage Products
Muottitie 2A, P.O.Box 622, FIN-65101 VAASA, 芬兰

产品名称和系列、规格、型号

隔离开关熔断器组

OS200D, OS200B, OS200J, OS250D, OS250B, OS200DZ, OS200DS, OS250DS具体规格见附件

产品标准和技术要求

GB14048.3-2008

上述产品符合强制性产品认证实施规则
CNCA-01C-011:2007的要求, 特发此证。

发证日期: 2011年03月29日

有效期至: 2016年03月29日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书, 证书首次颁发日期: 2005年03月02日

本证书的相关信息可通过国家认监委网站www.cnca.gov.cn查询



主任:

中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>



Q 0387462



中国国家强制性产品认证证书

附录:

Appendix:

证书编号: 2005010302143043

第 1 页 共 2 页

Page 1 of 2

纸号: 387462

规格型号: OS200D, OS200B, OS200J, OS250D, OS250B, OS200DZ, OS200DS, OS250DS

额定绝缘电压(Ui): 1000V;

约定发热电流(Ith): OS200D, OS200B, OS200J, OS200DS: 200A; OS200DZ: 160A;
OS250D, OS250B, OS250DS: 250A;

额定工作电压(Ue): OS200J: 600V;

OS200D, OS200B, OS250D, OS250B, OS200DZ, OS200DS, OS250DS: 2P: 500V, 690V;
3P, 4P :

415V, 500V, 690V;

额定工作电流(Ie): OS200D, OS200B, OS200J, OS200DS: 200A; OS200DZ: 160A;
OS250D, OS250B, OS250DS: 250A;

额定限制短路电流(Iq):

OS200D, OS200B, OS200DS: 2P: 100kA/500V; 80kA/690V;
3P: 50kA/415V; 80kA/415, 690V; 100kA/500V;
4P: 100kA/415, 500V; 80kA/690V;

OS250B: 2P: 100kA/500V; 80kA/690V;
3P: 50kA/415V; 80kA/500, 690V;
4P: 65kA/415V; 50kA/500, 690V;

OS250D, OS250DS: 2P: 100kA/500V; 80kA/690V;
3P: 80kA/415, 500, 690V;
4P: 100kA/415, 500V; 80kA/690V;

OS200J: 100kA/600V;

OS200DZ: 100kA/500V; 80kA/690V;

使用类别: AC-21A, AC-22A, AC-23A;

极数: 2P, 3P, 4P; 型号解释见下页

注: 此附录与证书同时使用时有效。



主任:

中国质量认证中心

中国·北京·南四环西路188号9区 100070

<http://www.cqc.com.cn>





中国国家强制性产品认证证书

附录:

Appendix:

证书编号: 2005010302143043

第 2 页 共 2 页

Page 2 of 2

纸号: 387462

OS200	D	S	03	H	F	P
						P=handle&shaft included K=direct handle Blank=without handle&shaft
						Fourth pole F=fused neutral N1=switched neutral on left side N2=switched neutral on right side N3=a detachable neutral link integrated into the mechanism
						H=silver layer 20 μ Blank=silver layer 7 μ
						Poles(according to side of mechanism) 2 poles- 11 20 02 3 poles- 12 21 03 or 30 4 poles- 13 31 22 04 or 40 1 Number= number of poles on left side 2 Number= number of poles on right side
						Blank=front operated S=side operated
						Type of fuse holder B= BS D=D-type fuse DIN 0 DZ=D-type fuse DIN 00 J=fuse J
						Basic type OS200, OS250

注: 此附录与证书同时使用时有效。



主任:

中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

No. : 2005010302143043

NAME AND ADDRESS OF THE APPLICANT

ABB Oy, Low Voltage Products
Muottitie 2A, P.O.Box 622, FIN-65101 VAASA, Finland

NAME AND ADDRESS OF THE MANUFACTURER

ABB Oy, Low Voltage Products
Muottitie 2A, P.O.Box 622, FIN-65101 VAASA, Finland

NAME AND ADDRESS OF THE FACTORY

ABB Oy, Low Voltage Products
Muottitie 2A, P.O.Box 622, FIN-65101 VAASA, Finland

NAME, MODEL AND SPECIFICATION

switch-disconnector-fuse

OS200D, OS200B, OS200J, OS250D, OS250B, OS200DZ, OS200DS, OS250DS; Model and specification see the appendix

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB14048.3-2008

This is to certify that the above mentioned products have met the requirements of implementation rules for compulsory certification(REF NO. CNCA-01C-011:2007).

Date of issue: Mar. 29, 2011 Date of expiry: Mar. 29, 2016

Validity of this certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original certification: Mar. 02, 2005

This certificate can be verified through CNCA's website: www.cnca.gov.cn



President:

Wang Kejiao

CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China

<http://www.cqc.com.cn>



Q 0387462