


AP300 Series Combination pH/Redox (ORP) Sensors

A reliable economic solution
for a wide range of applications



Long life

- large PTFE junction provides resistance to fouling
- double junction with gelled electrolyte provides better-defined junction potentials, creating an inherently-stable reference junction that is resistant to poisoning

High accuracy

- specially formulated, low sodium-error glass for accuracy at high pH
- temperature sensor positioned perfectly to compensate for measurement and reference element temperature, ensuring rapid compensation and process temperature tracking

High reliability

- operates up to 105 °C (221 °F) and 6 bar (90 psi) @ 25 °C (77 °F)
- fouling-resistant flat glass available

High flexibility

- suitable for a wide range of applications
- available for insertion, immersion, flow-through and hot-tap
- standard- and blue-glass options
- bulb and flat-glass options

Economical

- cost-effective
- long life
- highly reliable

Introduction

ABB provides an unrivalled range of dedicated pH/Redox (ORP) sensors for a wide range of industrial duties.

The AP300 range of pH/Redox sensors offers a reliable and cost-effective solution for most industrial pH applications. It is the perfect starting point for pH or Redox measurements.

Combining measurement, reference and temperature compensation elements in a single unit, the AP300 is an economical solution for a wide variety of industrial applications; including water, food, pharmaceutical and chemical.

The AP300 probe is available in three different body types enabling the sensor to be used in immersion, insertion/flow-through and hot-tap applications.

The 'Hot-tap' sensor variant enables fitting and retraction through a standard, full-port ball-valve keeping maintenance costs to a minimum.

Robust Design, Maximum Protection

The electrolyte is a highly resistant gel, faced with a large area, dirt-resistant PTFE junction. These are encapsulated in a robust body, providing maximum resistance to chemical attack. The sensor can withstand operating conditions up to 105 °C and 6 bar @ 25 °C (221 °F and 90 psi @ 77 °F).

Insertion, Flow-through, Immersion (Dip) and Hot-tap

AP301


General-purpose in-line/immersion, twistlock sensors.

The AP301 is a PPS (Ryton) sensor for general applications that can be adapted to 1 in. NPT fittings using threaded twistlock process adapters. Dip-type immersion is achieved using an immersion guard and connection of the $\frac{3}{4}$ in. NPT back-thread to a customer-supplied dip-tube.



AP301 Sensor with Optional Immersion Guard

For flow-through applications, a flow cell can be fitted with either 1 in. BSP (part no. 7670043) or 1 in. NPT (part no. 7670046) threaded process connections.



Optional Flow Cell (Flow-through)

AP300 Series
Combination pH/Redox (ORP) Sensors

AP302 and AP303

General-purpose insertion, flow-through, immersion, 3/4 in. NPT threaded sensors.

The AP302 and AP303 are constructed from PVDF (Kynar) and can be used in insertion/flow- or dip/immersion applications.

AP302 models have no sensor guard (flush) for use with flat glass to provide a flow-cleaned configuration.


AP303 models have a notched sensor guard to protect the bulb glass.



AP303 Notched Sensor

Flat / Notched Sensor

Notched sensors are provided to protect the bulb glass and are especially suited to retractable and immersion sensors.



Applications for Sensor Styles


AP304 and AP305

General-purpose, hot-tap retractable sensors.

Completing the series, the AP304 and AP305 are fully-retractable PVDF stainless steel-clad sensors. With these sensors, project and maintenance costs can be reduced significantly as the need for expensive by-pass systems or long immersion sensors are eliminated.



Hot-tap Retractable Sensor



AP304 and AP305 Anti-blowout Tip and Hand-compression Fitting Safety Features


AP300 Series

Combination pH/Redox (ORP) Sensors


Hot-tap Sensor

The safety of operators is paramount. This is maintained by incorporating an anti-blowout tip in the design of the AP304 & AP305; preventing accidental sensor removal. Unlike chain restraints, this safety-by-design is an integral part of the sensor's construction.

Ball-valve connection is achieved with either wrench or hand fittings. The hand compression fitting provides additional safety through two separate locking rings. A body nut union ring locks the sensor to the ball valve and enables sensor dismounting without complete disassembly. In addition, a compression ring fixes the sensor into position at the required insertion depth and seals the body from the process. This compression ring has an integral shroud that prevents access to the smaller body nut when the compression ring is loosened for sensor maintenance.



AP304/5 Compression Fittings



AP304 Hot-tap Sensor – Typical Installation



AP305 Hot-tap Sensor

Double Junction for Long Life

To maximize the life-span of the sensor, the AP300 features an inherently-stable, double junction arrangement. In addition, the sensor is designed to resist poisoning in two ways, by:

- effectively doubling the length of the diffusion path between the PTFE interface and the electrode, so any poisoning from the sample takes longer to reach it.
- discouraging any movement of the reference gel around the electrode by enclosing it in a glass tube open only at the top.




Double Junction Construction

Temperature Compensation

The AP300's temperature compensator offers fast response and high accuracy. The temperature sensor is located at the tip of the AP300, together with the measuring and reference electrodes. This arrangement provides accurate process temperature measurement used to compensate for the effects of temperature on the electrodes to produce a precise pH measurement.

The temperature compensator is available as Balco 3k or Pt100.



Temperature Compensation

AP300 Series
Combination pH/Redox (ORP) Sensors

Glass Options

The AP300 range is available with ABB's specially formulated standard pH-sensitive glass or, optionally, with low-resistance glass that speeds up the response of the sensor by an order of magnitude at temperatures below 60 °C (140 °F). For applications with higher pH levels and temperatures, ABB's standard glass offers a much lower sodium error than competing products; enabling the sensor to maintain its accuracy even at very high pH levels, when sodium ions would otherwise cause inaccurate readings.


Sodium error at 25 °C (77 °F): 0.02pH in 1M NaOH



ABB-manufactured Electrodes

Flat-glass


The flat end and glass design promotes self-cleaning and provides maximum resistance to fibrous build-up.



Flat and Bulb Glass Variants

Cable Options


Several connections are possible from the probe. An integral cable with tagged pins for direct connection to a transmitter or a male BNC connector for connection to an extension cable. Both tagged and BNC cables are available in versions that accommodate temperature signals. Cables are available in short, junction box-only lengths and 5 m (16 ft), 10 m (33 ft), 20 m (66 ft) and 30m (98 ft) lengths.




Sensor Cables and Junction Box Wiring

Overall Dimensions


AP301



AP302 and AP303



AP304 and AP305



AP300 Series

Combination pH/Redox (ORP) Sensors

Specification

General

pH measuring range

Standard (yellow glass)	0 to 14 pH
Low Temperature (blue glass)	0 to 10 pH

Redox (ORP) measuring range

-2000 to 2000 mV

Temperature range

Body	0 to 105 °C (32 to 221 °F)
Bulb glass	0 to 105 °C (32 to 221 °F)
Flat glass	5 to 100 °C (41 to 212 °F)
Blue glass	-5 to 60 °C (23 to 140 °F)
Redox (ORP)	0 to 105 °C (32 to 221 °F)

Pressure maximum

6 bar (90 psi) @ 25 °C (77 °F)

Temperature compensator (pH sensors only)

Integral Pt100 or Balco 3 kΩ

Wetted materials

pH electrode	Glass
Redox (ORP) electrode	Platinum
Junction	PTFE
Body AP301	PPS (Ryton)
Body AP302/3 and AP304/5	PVDF (Kynar)
Flow cell	PVC
Immersion guard	PVC
AP304 and AP305 shaft and valve	Stainless steel

pH glass types

Bulb	general duties
Flat	in-line, self-cleaning
Blue	low temperature

Reference system

Ag/AgCl-3.5M KCl in gel matrix

Reference junction

Porous PTFE

Spares and Accessories

Threaded lock-nut adapter, PPS (Ryton) (1 in. NPT)	4TB9515-0120
PVC Immersion/dip guard	4TB5205-0120
Junction box (requires cable gland)	4TB5023-0162
Cable gland	4TB9515-0244

Flow Cells

1 in. NPT (for adapter) + 1 in. NPT (for process connection)	7670 046
1 in. NPT (for adapter) + 1 in. BSPT (for process connection)	7670 043

Flow Cell Pipeline Adapters

1 in. BSPT to 1/2 in. BSPT polypropylene	7601 420
1 in. BSPT to 1/2 in. NPT polypropylene	7601 430

Extension Cables

Tagged pin extension cables (5-core 1015/16X for AX460 and AX466)	
5 m (16 ft)	1015 160
10 m (33 ft)	1015 161
20 m (66 ft)	1015 162
30 m (98 ft)	1015 163

Buffer Sachets (Box of 25)

4 pH	0400/110
7 pH	0400/120
0 pH	0400/130

Ordering Information

pH/Redox (ORP) Sensor/Assembly	AP30	X	/	X	X	0	X	X	XX	X
Gel-filled, disposable sensor with dirt-repellent PTFE junction										
Body style										
Twist-lock insertion/immersion (TB551 style)										
Standard insertion – no sensor guard (flush)		1								
³ / ₄ in. threaded insertion/immersion (TB556 style)										
Insertion depth 28 mm (1.1 in.) – no sensor guard (flush)		2								
Insertion depth 38 mm (1.5 in.) – notched sensor guard		3								
Hot-tap ball valve insertion (TB557 style)										
No sensor guard (flush)		4								
Notched sensor guard		5								
Measuring Electrode										
Flat glass pH for in-line, fouling applications (5 to 100 °C [41 to 212 °F], 0 to 14 pH)		1								
Standard yellow glass, pH (0 to 105 °C [32 to 221 °F], 0 to 14 pH)		2								
Low resistance blue glass, pH (–5 to 60 °C [23 to 140 °F], 0 to 10 pH)		3								
Platinum, Redox (ORP)		5								
Integral Temperature Sensor										
None – Redox (ORP) sensors only						0				
Pt100 – pH sensors only						1				
3 kΩ – pH sensors only						2				
Liquid Junction										
Teflon							0			
Junction Box or Integral Cable Length										
Short length cable – supplied without junction box								0		
3 m (10 ft)								1		
6 m (20 ft)								2		
9 m (30 ft)								3		
Integral junction box supplied with short length cable								8		
Sensor Connectors										
Tagged Pin Leads – all tagged terminations									0	
Connectors – BNC on pH/Redox (ORP) + temperature compensator connector (if used)									1	
Also select for electrodes used with junction box										
Accessory Hardware										
No accessory supplied										00
For AP301										
1 in. NPT, twist-lock adapter – Ryton (PPS)										12
PVC immersion (dip) guard										13
For AP304 & AP305										
406 mm (16 in.) stainless steel sheath										20
406 mm (16 in.) stainless steel sheath and 316 stainless steel wrench fitting										21
406 mm (16 in.) stainless steel sheath and 316 stainless steel hand fitting										22
508 mm (20 in.) stainless steel sheath										23
508 mm (20 in.) stainless steel sheath and 316 stainless steel wrench fitting										24
508 mm (20 in.) stainless steel sheath and 316 stainless steel hand fitting										25
Instruction Manual										
No manual supplied (replacement sensors only)										0
English										1
French										2
German										3
Spanish										4

Contact us

ABB Limited

Process Automation

Oldends Lane
Stonehouse
Gloucestershire GL10 3TA
UK

Tel: +44 1453 826 661

Fax: +44 1453 829 671

ABB Inc.

Process Automation

125 E. County Line Road
Warminster
PA 18974
USA

Tel: +1 215 674 6000

Fax: +1 215 674 7183

www.abb.com

Note

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents in whole or in parts – is forbidden without prior written consent of ABB.

Copyright© 2010 ABB

All rights reserved

3KXA163301R1001

DS/AP300-EN Rev. E 12.2010