

Data sheet DS/2867-EN Rev. E

2867 Series pH and Redox (ORP) Industrial Dip Electrode Systems



Simple, robust design in three dip lengths

Positive salt-bridge flow from integral reservoir

Easily-replaced, reliable combination electrode

Built-in sight glass for salt-bridge reservoir

Simple installation on wall or tank

Introduction

2867 Series industrial dip electrode systems are designed for pH and Redox measurement in channels and open tanks. It is particularly suitable for use in effluent treatment applications where automatic temperature compensation is not required. The 2867 utilizes a specially designed combination electrode, providing reliable measurement in a wide variety of samples.

The systems are constructed from plastic throughout; the dip stem, of nominal 0.46m, 0.92m or 1.83m (18 in., 3 ft or 6 ft) length, is manufactured in ABS which is chemically resistant to most samples and withstands temperatures of up to 70°C (158°C). The stem is filled with salt-bridge solution, forming an integral reservoir for the reference element mounted in the upper end of the electrode assembly. A liquid junction with the sample is made at a ceramic plug fitted in the wall of the stem at its lower end; two sizes of plug are provided, giving the option of a higher flow of salt-bridge solution in samples which would block the ceramic or contaminate the reference element.

Electrodes Available for the System

Glass combination pH electrode:

1912-400 (BNC plug termination)

1912-500 (tag terminations)

Antimony combination pH electrode:

(for samples containing Hydrofluoric Acid)

1990-400 (BNC plug termination)

1990-500 (tags)

Platinum combination Redox electrode:

1980-400 (BNC plug termination)

1980-500 (tags)

Each electrode assembly screws into the lower end of the system and is sealed by means of an 'O' ring to prevent salt-bridge solution loss. The fitted cable of 6m (19.5 ft) length passes out of the top of the system through a split rubber bung. The cable terminates in either a BNC plug (-400 electrodes), for connection to an extension cable or tags (-500 electrodes) for direct connection to 4500, 4600 and AX400 Series transmitters.

Mounting of the systems is achieved by using either the supplied flange or wall-mount bracket, with immersion depth adjustable by means of 'O' rings.

Extension cables for use with 9140, 9160, 4500 and 4600 Series

To connect model 4630/35, 4500 or AX400 Series transmitters to a 19XX type electrode over a distance of more than 6m, the 19XX-400 type electrodes should be specified together with an extension cable (part no. 9170-300) which has a BNC socket on one end and tags on the other end. 19XX-500 electrodes, with tag ends to their leads, are designed for direct connection to 4500, 4600 and AX400 Series transmitters.

The recommended maximum cable run is 100m (325 ft).

Specification

Material of construction

ABS (Acrylonitrile Butadiene Styrene) with perspex sight tube

Resistance of ABS to common chemicals at 25°C (77°F)

Sulphuric Acid (<50%)	Good
Nitric Acid (<50%)	Good
Hydrochloric Acid	Good
Phosphoric Acid	Good
Common Alkalis	Excellent
Alcohols	Good
Hydrocarbon Solvents	Unsuitable
Detergents	Excellent

Sample temperature range

0° to 70°C (32 to 158°F)

Mounting

By wall bracket or flange supplied, located by 'O' rings

Nominal stem lengths and weights

2867-500	0.46m (18 in.)	750g (29.5 lb)
2867-600	0.92m (3 ft)	850g (33.5 lb)
2867-700	1.83m (6 ft)	1350g (53 lb)

Electrodes

pH (glass) combination

1912-400 (BNC plug)

1912-500 (tags)

pH range 0 to 14

Temperature range -5° to +70°C (23 to 158°F)

Lead 6m (19.5 ft) length

pH (antimony) combination

1990-400 (BNC plug)

1900-500 (tags)

pH range 0 to 10

Temperature range -5° to +70°C (23 to 158°F)

Lead 6m (19.5 ft) length

Redox (platinum) combination

1980-400 (BNC plug)

1980-500 (tags)

Temperature range -5° to +70°C (23 to 158°F)

Lead 6m (19.5 ft) length

Electrolyte

3.8M KCl (part number 0400-170)

Service Pack (2867-041)


Comprising:

1 neoprene 'O' ring, 4 rubber 'O' rings, bung, 1 each 1.5mm and 3.5mm ceramic plugs, ceramic plug spanner

Spare ceramic plugs can be ordered separately under part numbers as follows:

1.5mm	2867-540
3.5mm	2867-550

Overall Dimensions



Contact us

ABB Limited

Process Automation

Oldends Lane
Stonehouse
Gloucestershire GL10 3TA
UK

Tel: +44 1453 826 661

Fax: +44 1453 829 671

ABB Inc.

Process Automation

125 E. County Line Road
Warminster
PA 18974
USA

Tel: +1 215 674 6000

Fax: +1 215 674 7183

www.abb.com

Note

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents in whole or in parts – is forbidden without prior written consent of ABB.

Copyright© 2011 ABB

All rights reserved

3KXA163801R1001

DS/2867-EN Rev. E 03.2011