



Configuration

The system consists of a spectroradiometer with two input and two output ports.

The system features simultaneous data acquisition from the two output ports (configured with a MCT and an InSb detector).

One input port is used to fix a reference cancellation source. The other input port is designed to receive an input telescope and a viewing device.

The MR304SC is equipped with stirling cooled detectors.

The spectroradiometer includes:

- Complete Fourier Transform Interferometer, with two detectors
- Electronic controls built into the FTIR module
- External power supply module
- Acquisition and data processing radiometric software
- Input collimator
- FTIR Internal temperature control system
- FTIR base with handles and fixation points for tripods
- Room temperature cancellation reference source
- Aluminum transport case

Data acquisition and radiometric software

Communication link to PC

100 Mb Ethernet communication with shielded CAT 5 cable

Recording time (continuous mode)

Up to 30 minutes (equivalent to 5 GB)

Transfer to hard disk

Data saved in real time to hard disk

Data time stamping

On-board, at ZPD from embedded processor

FTSW500 radiometric software (features)

- Control of the instrument (configuration, status, commands, etc.)
- Real time data acquisition on both channels (MCT and InSb det.)
- Functionalities to perform instrument diagnostics
- Data analysis and post processing
- Built-in radiometric calibration function (Radiance, Irradiance and Apparent Intensity)
- Built-in data export function to Galactic GRAMS 32
- Library of java functions compatible with MATLAB and IDL for further for further data processing
- Windows XP compatible

Options

Telescopes

- Wide-angle telescope (maximum field of view = 75 mrad)
focusing range: 2 m to infinity
- Medium-angle telescope (maximum field of view = 28 mrad)
focusing range: 10 m to infinity
- Narrow-angle telescope (maximum field of view = 4.9 mrad)
focusing range: 30 m to infinity

Viewing devices

- Ocular
- CCD camera with controller and monitor

Others

- Tripod
- Computer

Spectrometric characteristics

Spectral technique

Fourier Transform Interferometer

Spectral range

667 - 5,000 cm^{-1} (2-15 μm) capability

FOV uniformity

+ 7.5% on 85% of measured FOV

Spectral resolution

6 computer selectable unapodized resolutions (1, 2, 4, 8, 16, and 32 cm^{-1}) at all wavelengths

Spectral stability

Better than 0.01 cm^{-1}

Scan speed

23.5 cm/s , fixed

Scan rate

82 spectra per second at 16 cm^{-1} apodized resolution

FOV of interferometer

45 mrad (without input collimator or telescope)

Maximum optical throughput

$8.1 \times 10^{-3} \text{ cm}^2 \text{ sr}$

Detectors

InSb: 1,800-5,000 cm^{-1} (2-5.5 μm)

MCT: 667-2,500 cm^{-1} (4-15 μm)

Detector cooling

Stirling cryocooler

Noise equivalent spectral radiance

(at 16 cm^{-1} resolution, 1 s. observation time, calibration and measurement near ambient temperature, measured at peak response)

MCT: NESR (RMS) $< 2.5 \times 10^{-9} \text{ W cm}^{-2} \text{ sr}^{-1} \text{ cm}^{-1}$

InSb: NESR (RMS) $< 2.5 \times 10^{-10} \text{ W cm}^{-2} \text{ sr}^{-1} \text{ cm}^{-1}$

Dynamic range InSb detector

1-64 gain and 16-bit ADC

Dynamic range MCT detector

1-256 gain and 16-bit ADC

Gain control

Computer controlled (manual and automatic mode) in steps of 1, 2, 4, 8, 16, 32, 64 (128, 256 MCT only)

FOV selection

Computer-controlled field stop

Physical and electrical characteristics

Weight

Sensor head: 35 kg

Power supply module: 3.5 kg

Dimensions (L x W x H)

Spectroradiometer: 390 mm x 375 mm x 390 mm

Input collimator: 190 mm x 102 mm x 115 mm

Power supply module: 390 mm x 255 mm x 110 mm

Modulation frequency

15.7 kHz to 117.5 kHz

Temperature operation range

0°C to 45°C operating, -30°C to 55°C survival

Humidity

$< 90\%$ relative humidity non condensing

Operational random vibration

Acceleration spectral density 0.015 g^2/Hz from 5 to 40 Hz. Monotonic slope down to 0.0015 g^2/Hz at 500 Hz. (Along typical mounting direction)

Acceleration magnitude 1 g RMS along typical mounting direction (0.63 g RMS for the other 2 directions)

Reference to MIL-STD 810 F method 514.5

Shock

Optical head 6 g during 10 ms

Acceleration amplitude 6 g (half sine)

Shock duration 10 ms

Number of shocks 15 (5 each direction)

Reference to MIL-STD 810 method 516.5



ABB

Analytical

585, boulevard Charest E., suite 300

Québec, Qc G1K 9H4

Canada

Phone: 418-877-2944

Fax: 418-877-2834

Email: ftir@ca.abb.com

www.abb.com/analytical

MR304SC spec B4242 2005-05

Copyright © 2004 by ABB Inc. All rights to trademarks reside with their respective owners. Specifications subject to change without notice. Pictures, schematics and other graphics contained herein are published for illustration purposes only and do not represent product configurations or functionality. User documentation accompanying the product is the exclusive source for functionality descriptions.