

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES
FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEMESYSTEM CEI D'ACCEPTATION MUTUELLE DE CERTIFICATS D'ESSAIS
DES EQUIPEMENTS ELECTRIQUES (IECEE) METHODE OC

CB TEST CERTIFICATE

CERTIFICAT D'ESSAI OC

Product Produit	Contactors
Name and address of the Applicant Nom et adresse du demandeur	ABB Stotz-Kontakt GmbH Eppelheimer Strasse 82 PO Box 101680 69123 HEIDELBERG Germany
Name and address of the manufacturer Nom et adresse du fabricant	ABB Stotz-Kontakt GmbH Eppelheimer Strasse 82 PO Box 101680 69123 HEIDELBERG Germany
Name and address of the factory Nom et adresse de l'usine	Avist Eood Ilarion Makariopolski Str. 5 2850 PETRICH Bulgaria
Rating and principal characteristics Valeurs nominales et caractéristiques principales	See page 2
Trademark (if any) Marque de fabrique (si elle existe)	ABB
Type of manufacturer's Testing Laboratories used Type de programme de laboratoire d'essais constructeur	WMT
Model / Type Ref. Réf. de type	EH04-11 and EH04-20
Additional information (if necessary may also be reported on page 2) Les informations complémentaires (si nécessaire, peuvent être indiquées sur la 2ème page)	Re-issue of BE-3011 dated 2011-07-05 due to non-technical change : typing error in the product reference. For details refer to test report.
A sample of product was tested and found to be in conformity with IEC Un échantillon de ce produit a été essayé et été considéré conforme à la CEI	60947-5-1(ed.3);am1 Comments: All requirements acc. to GB14048.5-2008 and GB14048.1-2006 are met.
As shown in the test report Ref. No. which forms part of this certificate Comme indiqué dans le rapport d'essais numéro de référence qui constitue partie de ce certificat	58207603/00 up to 58207603/07

This CB Test Certificate is issued by the National Certification Body:

Ce Certificat d'essai OC est établi par l'Organisme National de Certification

SGS Belgium NV - Division SGS CEBEC
Riverside Business Park Avenue Internationalelaan 55 Build. D B - 1070 Brussels,
Belgium

Date: 2011-07-20

Signature: Calogero LANA

page 1 of 1

Ratings:

rated operational voltage (Ue)	:	500 V
rated insulation voltage (Ui)	:	500 V
rated impulse withstand voltage (Uimp)	:	4 kV
conventional free air thermal current (Ith)	:	6 A
rated frequency	:	50 / 60 Hz
utilization category	:	AC-15
rated conditional short-circuit current	:	1 kA
backup protection	:	fuse
degree of protection	:	IP 20
pollution degree	:	2
suitability for isolation	:	No

Further Data:

The EH04-xx auxiliary switches are designed for side mounting to the ESB24, ESB40 or ESB63 contactors.

They have to sets contacts operated by the ESB device.

There are two variants available, EH04-20 with 2 NO contacts and EH04-11 with one NO and one NC contact.

Utilization Category	Ue (V)	Ie (A)	
		NC	NO
AC-15	120V	6 A	6 A
	240V	4 A	4 A
	415V	1 A	3 A
	500V	1 A	2 A
