



# Type Approval Certificate

Germanischer Lloyd

This is to certify that the undernoted product(s) has/have been tested in accordance with the relevant requirements of the GL Type Approval System.

Certificate No.	1131898 HH
Company	ABB SACE S.p.A Via Baioni 35 24123 Bergamo, ITALY
Product Description	Air Circuit Breaker
Type	E3H08, E3H10, E3H12, E3H16, E3H20, E3H25, E3H32 Series EMAX, 3-pole
Environmental Category	C
Technical Data / Range of Application	Rated current In : 250-1250 / 250-1600 / 250-2000 / 250-2500 / 250-3200 A Rated operational voltage Ue: 690 V AC Rated insulation voltage Ui : 1000 V Rated impulse voltage Uimp : 12 kV Rated frequency : 50/60 Hz Utilization category: B  Rated short-circuit capacity : Performance at : 440 / 690 V Icm [kA] : 220 / 187 kA Icu [kA] : 100 / 85 kA Ics [kA] : 85 / 85 kA Icw [kA] : 75 kA, (1 sec) Release system: SACE PR111, PR112, PR113, PR121, PR122 and PR123 (L, S, I, G) Communication port for monitoring purposes only
Test Standard	Guidelines for the Performance of Type Approvals (2003) IEC 947-2 (1989), EN 60947-2 (1991-10) Amendment 1 (1997) Annex H
Documents	Test report : ACAE-LOVAG No. IT 97.001 to 97.004, 97.011, 97.026 to 97.033, 97.035 to 97.037, 01.034 SINAL No. IA/TTR-97/005, Mariperma No. 9466, 9467 ABB SACE No. 10334, 10335, ETL SEMKO C133_06, C133_08, E13306, E13307, E13308, E13309, ACAE 05-033, 05-034
Remarks	None
Valid until	2016-11-21
Page	1 of 1
File No.	I.K.01
Hamburg, 2011-11-22	

Type Approval Symbol



Germanischer Lloyd

Christoph Kutzner

Harald Amberger

This certificate is issued on the basis of "Regulations for the Performance of Type Tests, Part 0, Procedure".