



Certifié conforme à l'original

le 28 SEP. 2001

Le bureau de gestion de l'ASEFA

G.GOSSE



Certificate of Conformity

LOVAG-Certificate No. FR 01-025

Apparatus : three-pole contactor

Designation : BC 16-30-10

Manufacturer or responsible vendor

ABB CONTROL
10, rue Ampère - ZI - BP 114
69685 CHASSIEU - FRANCE

Tested for: ABB CONTROL

Tested by: ASEFA platform G03

This Certificate applies only to the apparatus tested. The responsibility for conformity of any apparatus having the same designation with that tested rests with the manufacturer or responsible vendor.

This certificate has been prepared according to LOVAG (Low Voltage Agreement Group) Objectives and Operating Principles or mutual recognition. The responsible certification body, as member of LOVAG, issues a Certificate of Conformity with the above mentioned Standard(s) following the exclusive use of LOVAG Test Instructions wherever applicable.

Only integral reproduction of this Certificate or reproductions of this page accompanied by any page(s) on which are stated the tests performed and the assigned rated characteristics of the apparatus tested, are permitted without written permission from the LOVAG Signatory responsible for this Certificate.

The apparatus, constructed in accordance with the description mentioned in the Test Report listed on this Certificate has been subjected to the series of proving tests in accordance with IEC 60947-4-1(1990-05) corrigendum (1991-12) amendment 1 (1994-11) and amendment 2 (1996-08) - EN 60947-4-1 (1992-01) amendment 1 (1995-01) and amendment 2 (1997) - Test sequences II and III.

The results are shown in the Test Report in accordance to LOVAG. The values obtained and the general performance are considered to comply with the above Standard(s) and to justify the characteristic assigned by the manufacturer as stated below.

Main circuit 3-pole $U_i = 690 \text{ V}$, 50 Hz $I_{th} = 25 \text{ A}$

Sequence II

Operational voltage : $U_e(\text{V})$	≤ 440	$> 440 \text{ \& } < 500$	$> 500 \text{ \& } \leq 690$
Operational current : $I_e(\text{A})$ AC-3	16	13	8
$I_e(\text{A})$ AC-4	16	13	8

Sequence III (AC1)

$U_e = 500 \text{ V}$ $I_e = 20 \text{ A}$ $I_p = 3 \text{ kA}$ $I_q = 25 \text{ kA}$

SCPD : fuses FERRAZ SHAWMUT 32 AgG ref. W 216656

Co-ordination type 1

Electrical control circuit : $U_s = 220 \text{ V}$ $U_i = 690 \text{ V}$

Auxiliary circuits : $I_{emax} = 6 \text{ A}$, 50Hz $U_i = 690 \text{ V}$

This document includes Report No.: G03 - 01179

Issue Date: 2001.08.14

Responsible Certification Body

I. HELLER

Authorized Signature

Date: 28 SEP. 2001