



# 中国国家强制性产品认证证书

证书编号: 2003010309065347

## 委托人名称、地址

ABB STOTZ-KONTAKT GmbH  
Eppelheimer Strasse 82 69123Heidelberg Germany

## 生产者(制造商)名称、地址

ABB STOTZ-KONTAKT GmbH  
Eppelheimer Strasse 82 69123Heidelberg Germany

## 生产企业名称、地址

ABB STOTZ-KONTAKT GmbH  
Eppelheimer Strasse 82 69123Heidelberg Germany

## 产品名称和系列、规格、型号

### 电动机保护用断路器

MS325, MO325 Ue: AC400, 500, 690V In: 0.16, 0.25, 0.4, 0.63, 1, 1.6, 2.5, 4, 6.3, 9, 12.5, 16, 20, 25A AC400V: Ics=Icu=100kA(0.16~9A), Ics=Icu=75kA(12.5A), Ics=Icu=60kA(16A), Ics=Icu=55kA(20A), Ics=Icu=50kA(25A)  
AC500V: Ics=Icu=100kA(0.16~2.5A), Ics=Icu=60kA(4A), Ics=Icu=40kA(6.3A), Ics=Icu=30kA(9A), Ics=Icu=27kA(12.5A), Ics=Icu=25kA(16A), Ics=Icu=22kA(20A), Ics=Icu=20kA(25A) AC690V: Ics=Icu=100kA(0.16~1.6A), Ics=Icu=40kA(2.5A), Ics=Icu=10kA(4A), Ics=Icu=7kA(6.3A), Ics=Icu=5kA(9A), Ics=Icu=4.5kA(12.5A), Ics=Icu=4kA(16A), Ics=Icu=3.5kA(20A), Ics=Icu=3kA(25A) 脱扣级别: 10A 使用类别: A 极数: 3P 配用的辅助触头 HKF: Ue/Ie: AC-15: 24V/4A, 120V/3A, 230V/2A, 400V/1A Ue/Ie: DC-13: 24V/2A, 120V/0.55A, 230V/0.25A

## 产品标准和技术要求

GB 14048.2-2008, GB 14048.4-2003

上述产品符合强制性产品认证实施规则  
CNCA-01C-011:2007的要求, 特发此证。

发证日期: 2010年02月09日

有效期至: 2015年02月09日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书, 证书首次颁发日期: 2003年07月23日

本证书的相关信息可通过国家认监委网站www.cnca.gov.cn查询



主任:

中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>



Q 0205923



# CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

No. : 2003010309065347

## NAME AND ADDRESS OF THE APPLICANT

ABB STOTZ-KONTAKT GmbH  
Eppelheimer Strasse 82 69123Heidelberg Germany

## NAME AND ADDRESS OF THE MANUFACTURER

ABB STOTZ-KONTAKT GmbH  
Eppelheimer Strasse 82 69123Heidelberg Germany

## NAME AND ADDRESS OF THE FACTORY

ABB STOTZ-KONTAKT GmbH  
Eppelheimer Strasse 82 69123Heidelberg Germany

## NAME, MODEL AND SPECIFICATION

Manual Motor Starters

MS325, MO325 Ue: AC400, 500, 690V In: 0.16, 0.25, 0.4, 0.63, 1, 1.6, 2.5, 4, 6.3, 9, 12.5, 16, 20, 25A AC400V: Ics=Icu=100kA (0.16~9A), Ics=Icu=75kA (12.5A), Ics=Icu=60kA (16A), Ics=Icu=55kA (20A), Ics=Icu=50kA (25A)  
AC500V: Ics=Icu=100kA (0.16~2.5A), Ics=Icu=60kA (4A), Ics=Icu=40kA (6.3A), Ics=Icu=30kA (9A), Ics=Icu=27kA (12.5A), Ics=Icu=25kA (16A), Ics=Icu=22kA (20A), Ics=Icu=20kA (25A) AC690V: Ics=Icu=100kA (0.16~1.6A), Ics=Icu=40kA (2.5A), Ics=Icu=10kA (4A), Ics=Icu=7kA (6.3A), Ics=Icu=5kA (9A), Ics=Icu=4.5kA (12.5A), Ics=Icu=4kA (16A), Ics=Icu=3.5kA (20A), Ics=Icu=3kA (25A) 脱扣级别: 10A 使用类别: A 极数: 3P 配用的辅助触头 HKF: Ue/Ie: AC-15: 24V/4A, 120V/3A, 230V/2A, 400V/1A Ue/Ie: DC-13: 24V/2A, 120V/0.55A, 230V/0.25A

## THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB 14048.2-2008, GB 14048.4-2003

This is to certify that the above mentioned products have met the requirements of implementation rules for compulsory certification (REF NO. CNCA-01C-011:2007).

Date of issue: Feb. 09, 2010 Date of expiry: Feb. 09, 2015

Validity of this certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original certification: Jul. 23, 2003

This certificate can be verified through CNCA's website: [www.cnca.gov.cn](http://www.cnca.gov.cn)



President:

Wang Kejiao

CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China

<http://www.cqc.com.cn>



Q 0205923