



1. **EC-TYPE EXAMINATION CERTIFICATE**
2. **Equipment or Protective Systems Intended for use in
Potentially explosive atmospheres
Directive 94/9/EC**
3. Reference: **VTT 06 ATEX 085X**
4. Equipment: **Range of cage induction motors**

Certified types: **M3GM 315...
M3GM 355...
M3GM 400...
M3GM 450...**
5. Manufactured by: **ABB Oy Machines**
6. Address: **Strömbergintie 1
FI-00380 HELSINKI
FINLAND**
7. These equipment and any acceptable variations thereto are specified in the schedule and possible supplement(s) to this certificate and the documents therein referred to.
8. VTT, notified body number 0537, in accordance with Article 9 of the Council Directive 94/9/EC of March 1994, certifies that the motors has been found to comply with the Essential Health and Safety Requirements relating to the design and construction of equipment and protective systems intended for use in potentially explosive atmospheres given in Annex II to the Directive
9. The examination and test results are recorded in confidential Report no FI/VTT/ExTR06.0003/00.
10. Compliance with the Essential Health and Safety Requirements has been assured by compliance with:
**EN 61241-0 (2006)
EN 61241-1 (2004)**



-
11. If the sign "X" is placed after the certificate number, it indicates that these equipment is subject to special conditions for safe use specified in the schedule to this Certificate
12. This EC-Type examination certificate relates only to the design, examination and tests of the specified equipment in accordance to the directive 94/9/EC.
- Further requirements of the Directive may apply to the manufacturing process and supply of these equipments. These are not covered by this certificate.
13. The marking of the equipment shall include the following:



II 2 D

Ex tD A21 IP65 or IP66 T125 °C

Espoo, 20.12.2006

VTT TECHNICAL RESEARCH CENTRE OF FINLAND



Martti Siirola
Research scientist



Jari Kettunen
Research engineer

14. **Schedule**15. **EC-TYPE EXAMINATION CERTIFICATE NO. VTT 06 ATEX 085X**16. Description of Equipment

Three phase squirrel cage induction motors of a closed type with external longitudinal cooling, cast iron frame and fitted out with Exe-certified main and Exi- or Exe-certified auxiliary terminal boxes. The duty type of the motors shall be S1.

Technical data

The Certificate is valid for the range of induction motors having the rated values within the limits in the following table:

Shaft height	U / kV	Number of poles	f / Hz	P / kW
315	up to 3.3	2 - 6	50	up to 800
355	up to 6.6	2 - 6	50	up to 800
400	up to 6.6	2 - 12	50	up to 800
450	up to 6.6	2 - 12	50	up to 800

17. Report No. FI/VTT/ExTR06.0003/0018. Special conditions for safe use

The Certificate covers also the frequency converter drive with the converter type ACS 1000-series, manufactured by ABB Group Ltd, at squared torque drive. All the manufacturer's instructions concerning the speed range and the moment restrictions shall be followed.

The motors may be indicated to be used in ambient temperature other than specified in the standards (-20 °C...+40 °C).

As an option motor can be delivered without main terminal box. Before commissioning, terminal arrangement shall be such that the stator connection cables are covered with earthed protective structure (e.g. main terminal box and adequate intermediate box). Main terminal boxes must fill following requirements:

- Ex-certified,
- Enclosure IP65 or higher according to site conditions.

19. Essential Health and Safety Requirements

Met by compliance with the standard EN 61241-1.

Espoo, 20.12.2006

VTT TECHNICAL RESEARCH CENTRE OF FINLAND



Martti Siirola
Research scientist



Jari Kettunen
Research engineer