



1	D-BEARING	6326M/C3
2	N-BEARING	6322/C3 INSULATED 6322/C3 (OPTIONAL)
3	TERMINAL BOX FOR CONTROL	CAPLE 10-14, 2xM20x1,5 LARGER TERMINAL BOX (OPTIONAL)
4	SPM NIPPLE	DE AND NDE
5	PT-100	FOR BEARINGS (OPTIONAL)
6	INTERMEDIATE BOX	
7	FREE DISTANCE FOR COOLING	
8	TERMINAL BOX FOR HEATING ELEMENT	CAPLE 10-14, 1xM20x1,5 (OPTIONAL)
9	GREASING NIPPLE	DE AND NDE
10	EARTHING, M12, FOR M3GM	MAX 150mm <sup>2</sup>
11	TRANSPORTATION COVER,	THREE (3) LEADS OUT 1.5m (5ft) SIX (6) LEADS OUT (OPTIONAL)

We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden.  
© ABB Oy, Machines, Helsinki

General tolerances ISO 2768-mK  
Threads according to ISO 965 tolerance class 6H  
Symbols for roughness acc. to ISO 1302

MAXIMUM MASS FOR MTB ASSEMBLY 600 kg,  
MAXIMUM MOMENT FROM MTB ASSEMBLY ACCORDING TO POINT W 1400Nm.

THE CUSTOMER IS RESPONSIBLE FOR THE DESIGN AND CONSTRUCTION OF THE FOUNDATION. IT SHALL BE SUFFICIENTLY RIGID TO WITHSTAND SHORT CIRCUIT FORCES. TO AVOID RESONANCE VIBRATIONS THE FOUNDATION SHALL BE DESIGNED SO THAT THE NATURAL FREQUENCY OF FOUNDATION TOGETHER WITH MACHINE IS NOT WITHIN ±20% OF RUNNING SPEED FREQUENCY. THE CUSTOMER IS ALSO RESPONSIBLE FOR LATERAL AND TORSIONAL CRITICAL SPEED ANALYSIS OF THE COMPLETE INSTALLATION.

BEFORE COMMISSIONING, TERMINAL ARRANGEMENT SHALL BE SUCH THAT THE STATOR CONNECTION CABLES ARE COVERED WITH EARTHED PROTECTIVE STRUCTURE (E.G. MAIN TERMINAL BOX AND ADEQUATE INTERMEDIATE BOX).

MAIN TERMINAL BOXES ARE NOT INCLUDED IN MOTOR MANUFACTURER'S DELIVERY.

MAIN TERMINAL BOXES MUST FILL FOLLOWING REQUIREMENTS:

- FOR EXPLOSIVE ENVIRONMENTS EX CERTIFIED
- ENCLOSURE IP55 OR HIGHER ACC. TO SITE CONDITIONS

Rev	Change	Date	Prep.	Approved	Scale
Prepared	2006-09-22 M.VÄKIPARTA	Responsible dept.	ATAP/PID	Title	1:25
Approved	2006-09-22 O.LAHTINEN	Take over dept.		DIMENSION PRINT SQUIRREL CAGE MOTOR	
Material		Code	13 BM 450_IEC A / 450	Language	en
Supersedes	Superseded by	Type	M3BM/GM 450L4-12 V1	Size	A3
ABB Oy, Machines, Helsinki		Document No.	3GZF500045-97	Revision	Sheet
			A		1/1