


PowerCube type PB/F

Fixed parts for constructing medium voltage switchgear


- Modular structure
- Mechanical and electromechanical safety locks against incorrect operations
- Metal shutters with fail safe device on request (prevention of manual opening)
- Suited to making switchgear for circuit-breaker/contactor racking-in/out with door closed
- Possibility of using gas insulated circuit-breakers and vacuum circuit-breakers and contactors
- Version with earthing switch with making capacity
- Earthing switch fitted with interlocks with the circuit-breaker



Technical data

PowerCube type PB/F		12 kV	17,5 kV	24 kV
Rated voltage	[kV]	12	17,5	24
Rated insulation voltage	[kV]	12	17,5	24
Withstand voltage (50 Hz)	[kV]	28	38	50
Impulse withstand voltage	[kV]	75	95	125
Rated frequency	[Hz]	50-60	50-60	50-60
Rated normal current (40 °C)	[A]	630	630	630
		1250	1250	1250
		1600	1600	-
Rated short-time withstand current	[kA]	2000	2000	-
		31,5	31,5	25
Overall dimensions (excluding monoblocs)	 H [mm] L [mm] P [mm]	1098	1098	1226
		596/746	596/746	746
		1061	1061	1338
Compatible circuit-breakers and contactors				
- HD4		•	•	•
- VD4		•	•	•
- VM1		•	•	•
- eVM1		•	•	-
- Vmax		•	-	-
- V-Contact		•	-	-

Main components



For more information please contact:

ABB S.p.A.
Power Products Division
Unità Operativa Sace-MV
 Via Friuli, 4
 I-24044 Dalmine
 Tel.: +39 035 6952 111
 Fax: +39 035 6952 874
 E-mail: sacetms.tipm@it.abb.com

ABB AG
Calor Emag Medium Voltage Products
 Oberhausener Strasse 33 Petzower Strasse 8
 D-40472 Ratingen D-14542 Glindow
 Phone: +49(0)2102/12-1230, Fax: +49(0)2102/12-1916
 E-mail: calor.info@de.abb.com

www.abb.com

The data and illustrations are not binding. We reserve the right to make changes without notice in the course of technical development of the product.

Copyright 2009 ABB.
 All rights reserved.