

Type Approval Certificate



This is to certify that the undernoted product(s) has/have been tested in accordance with the relevant requirements of the GL Type Approval System.

Certificate No. **89 800 - 94 HH**

Company **ABB AB**
LV Motors
Örjansgränd 31
721 70 Västerås, SWEDEN

Product Description **Induction motors**

Type **M2AA 160 up to M2AA 250 (Aluminium frame)**
M2BA 160 up to M2BA 250 (Cast iron frame)

Environmental Category **H**

Technical Data /
Range of Application

Sizes:	MLA, MLB, MLC, MLD, MLE, SMA, SMB, SMC
Rated voltage:	200 V up to 690 V
Rated power:	S1 7,5 kW up to 63 kW S2-30min up to 87 kW S6-25% up to 87 kW S6-40% up to 87 kW S6-60% up to 73 kW
Synchronous speed:	1000 1/min up to 3600 1/min
Rated frequency:	50 Hz, 60 Hz
Ambient temperature:	45° C, Thermal class 155 (F)
Duty type:	S 1, S2-30min, S6-25%, S6-40%, S6-60%
Degree of protection:	IP 55, IP 56
No. of poles:	2, 4, 6
Spec. model:	For marine environments

Valid for all variants independent of voltage, power and type of construction

Test Standard **IEC 60034-1 / 2010-02**

Documents **Drawings 3GZV 102 021-T Rev 10-36, 3GZV 102 033-A Rev 08-36**
Catalogue GAKK105496 EN06-2011, testreports of 22.3.94 / 15.9.03, 15.9.03 ABB
ATP AB 40572 STH/22-04-2002, 10774067003 / 2011-10-05
Test instruction (GL)3GZV 100 004-26 / ATMM/AT 96-39

Remarks **None**

Valid until **2016-11-10**

Page **1 of 1**

File No. **I.G.03**

Hamburg, **2011-11-11**

Type Approval Symbol



W. Voß

Wolfgang Voß

H. Hesper

Heinz-Dieter Hesper

Germanischer Lloyd