




We reserve all rights in this document and in the information contained therein. Reproduction, use for other than intended purposes, or distribution without the written permission of ABB Automation Technologies AB is strictly forbidden.



3-PHASE OVERCURRENT AND EARTH-FAULT PROTECTION



- 101 RTXP 18
- 107 RXTUG 22H
- 113 RXHL 401
- 125,325 RXME 18

- 1), 2) BINARY INPUT, PROGRAMMABLE
- 3)-7) RELAY OUTPUTS 1-5, PROGRAMMABLE FUNCTION
- 8) LOSS OF AUXILIARY VOLTAGE
- 9) CONNECTED FOR RL=110-220V DC

PROGRAMMABLE FUNCTIONS FOR BINARY INPUTS:
BLOCKING/ENABLING I>, I>>, I>>>, IN>, IN>>, IN>>>
ALTERNATIVE SETTINGS; RESET OF LED INDICATIONS.

PROGRAMMABLE FUNCTIONS FOR BINARY OUTPUTS:
START AND TRIP I>, I>>, I>>>, IN>, IN>>, IN>>>;
ALTERNATIVE SETTINGS; IN SERVICE

Customer drw no	Prep. PTUA/ TPTD H Raza/JE 2000-01-28	1MRK 001 082-CB	Lang. en	Rev. -	Sheet 1
	Appr. PTUA/ Roger Karlsson 2000-02-03	Circuit Diagram O/C and E/F protection			
	Resp. dept PTUA/ TPTD	Document number 1MRK001083-CB			
Based on	ABB ABB Automation Technologies				

Document status: Approved