



We reserve all rights in this document and in the information contained therein. Reproduction, use for other than intended purposes, or distribution without the written permission of ABB Automation Technologies AB is strictly forbidden.



MULTI-FUNCTION BREAKER FAILURE PROTECTION



101 RXTUG 22H
107 RXHB 41

- 1), 2) BINARY INPUT, PROGRAMMABLE
- 3)-7) RELAY OUTPUTS 1-5, PROGRAMMABLE FUNCTION
- 8) LOSS OF AUXILIARY VOLTAGE
- 9) CONNECTED FOR RL=110-220 V DC
CHANGE FROM 110 TO 112 AND 121 TO 122
AT RL=48-60 V DC

PROGRAMMABLE FUNCTIONS FOR BINARY INPUTS:
BREAKER FAILURE EXTERNAL START SIGNAL: IL1, IL2, IL3, 3-PHASE,
UNCONDITIONAL BREAKER FAILURE, CIRCUIT-BREAKER FAILURE;
BLOCKING BREAKER FAILURE AND POLE DISAGREEMENT; STORE
ACTUAL CURRENTS; RESET OF LED INDICATION.

PROGRAMMABLE FUNCTIONS FOR BINARY OUTPUTS:
RETRIP SIGNAL IL1, IL2, IL3, 3-PHASE; BACK-UP TRIP 1 SIGNAL;
BACK-UP TRIP 2 SIGNAL, POLE DISAGREEMENT START AND TRIP;
IN SERVICE

BINARY INPUT OPTIONS:
BLOCKING/ENABLING I>, I>>, IN>, IN>>;

BINARY OUTPUT OPTIONS:
START AND TRIP IL1>, IL2>, IL3>, IL1>>, IL2>>, IL3>>, MULTI-PHASE I>,
MULTI-PHASE I>>, IN>, IN>>.

Customer drw no	Prep. PTUA/ TPTD Eriksson Jill 2001-01-04	1MRK 002028-AA	
	Appr. PTUA/ TATD Karlsson Roger 2001-01-11	Circuit Diagram	
	Resp. dept PTUA/ TPTD	Multi-function breaker failure protection	
Based on	ABB ABB Automation Technologies		Document number
			1MRK002029-AA
	Lang. en	Rev. -	Sheet 1

Document status: Approved